

## DESCRIPTION

The CU2SQ Series offers quality and value with a compact and attractive LED based emergency light. The white or black housing and lamp-heads are made of high impact UL flame rated thermoplastic. The square LED lamp-heads are fully adjustable and glare-free. Snap together design for quick and easy installation with option of wall or ceiling mount. The remote capacity unit will run 2 Compass CIR/COR Series single remote lamp-heads or 1 double CIR/COR remote.

## APPLICATION

The CU2SQ Series can be applied in stair-wells, hallways, offices and commercial applications.

## COMPLIANCES

UL924 Listed for Damp Location  
 NFPA 101 and NFPA 70  
 OSHA

## WARRANTY

2 year full unit warranty



tradeSELECT™

## FEATURES

- LED life-cycle of more than 10 years
- Quick installation
- Dual-voltage 120 or 277V AC input
- Includes long-life Nickel Cadmium battery for UL recognized 90 minute emergency lighting
- Remote capacity or extended runtime option
- Damp Location Listed 20°C to 30°C (68°F to 86°F)
- Fully adjustable lamp-heads
- Provided with test switch and AC-On indicator
- Wall or Ceiling mount

## ENERGY CONSUMPTION


	120 VAC	277 VAC
CU2SQ	1.8 W	1.8 W
CU2RCSQ	2.5 W	2.5 W

## ORDERING GUIDE

Catalog Number	Description
CU2SQ	White Thermoplastic, Dual Square Head Emergency Light, 120/277VAC Input, Damp Location Listed, 3.6VDC Output, 0.79W per lamp
CU2SQB	Black Thermoplastic, Dual Square Head Emergency Light, 120/277VAC Input, Damp Location Listed, 3.6VDC Output, 0.79W per lamp
CU2RCSQ	White Thermoplastic, Dual Square Head Emergency Light, 120/277VAC Input, Damp Location Listed, 3.6VDC Output, 0.79W per lamp, 2.3W of remote capacity to run CIR/COR remotes

Note: Remote Capacity Unit will only power the Compass Indoor and Outdoor Remote(CIR and COR Series)

## DIMENSIONS



Single Carton Weight: 1 lbs.  
 Master Carton Quantity: 12 each

## ACCESSORIES

- WGLZ Wireguard - 6.25" H X 14" W X 4" D
- CIR Series - Matching LED Indoor Remote Heads
- COR Series - Matching LED Outdoor Remote Heads

