

TOOL-LESS FLANGED SPACER BLANKS



The Kendall Howard Flat Spacer Blanks are a cut above the rest. Spacer Blanks are often used as a way to fill in any gaps and conceal empty rack spaces in a rack or enclosure. The use of filler panels not only makes racks look neat, clean and organized, but when installed properly they provide added support to the mounting rails. These rack panels are also critical for controlling proper airflow especially in cold aisle/hot aisle applications.

FEATURES

Universal/Tool-Less Mounting - The panel features oblong mounting holes that are compatible with any standard rack hardware. However, the included tool-less clips make installation a breeze with any universal cage nut style rails.

Rounded Corners - The rounded corners and durable powder coat finish provide a smooth edge for safe handling and installation.

Proper Airflow - Using spacer blanks to fill the gaps and openings throughout your rack installation is especially important when thermal management is a concern. Not only will the filler panels prevent unwanted debris such as dust from getting in, but it will also prevent hot air from being recirculated into your equipment.

Professional Look - Installing rack panels in the unused rack mount spaces (RMS) gives your overall installation a clean and organized appearance.

Added Support - The two (2) 1/4" flanges on the top and bottom of the spacer blank increase the strength of the panel. This in turn helps to better support the rack rails and can even help shore up a server rack or cabinet.



SPECIFICATIONS

Size	1U	2U	3U	4U	6U
Part Number	1901-1-001-01	1901-1-002-02	1901-1-003-03	1901-1-004-04	1901-1-006-06
Width	19"	19"	19"	19"	19"
Depth	0.50"	0.50"	0.50"	0.50"	0.50"
Height	1.72"	3.47"	5.22"	6.97"	10.47"
Material(s)	CRS (Cold Rolled Steel)	CRS (Cold Rolled Steel)	CRS (Cold Rolled Steel)	CRS (Cold Rolled Steel)	CRS (Cold Rolled Steel)
Finish/Color	Black Powder Coat Finish	Black Powder Coat Finish	Black Powder Coat Finish	Black Powder Coat Finish	Black Powder Coat Finish
UPC	879447000115	879447000122	879447001570	879447000139	879447000146
Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty
Shipping Method	FedEx Ground	FedEx Ground	FedEx Ground	FedEx Ground	FedEx Ground