



- NOTE:
1. FAN TYPE: TUBE AXIAL
  2. VOLTAGE RATED: 115 VAC, 0.20 A
  3. AIRFLOW: TBD
  4. TERMINATION: 2 TERMINALS /NO GND

**PROPRIETARY AND CONFIDENTIAL**  
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF KENDALL HOWARD. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF KENDALL HOWARD IS STRICTLY PROHIBITED.

**WEB PRINT**

NEXT ASSY

USED ON

APPLICATION

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN INCHES  
TOLERANCES:  
FRACTIONAL  $\pm 1/8$   
ANGULAR: BEND  $\pm 1$  DEGREE  
TWO PLACE DECIMAL  $\pm .03$   
THREE PLACE DECIMAL  $\pm .01$

Surface Area

MATERIAL

FINISH

DO NOT SCALE DRAWING

	NAME	DATE
DRAWN	JL	10/25/13
CHECKED		
ENG APPR.		
MFG APPR.		
Q.A.		
COMMENTS:		

<b>KENDALL HOWARD</b>		
TITLE: <b>HIGH SPEED FAN ASSEMBLY</b>		
SIZE <b>A</b>	DWG. NO. <b>1908-4-001-01 WP</b>	REV <b>-</b>
SCALE: 1:4	WEIGHT: 0.94	SHEET 1 OF 1