

## Pro Fit® Washable USB Keyboard

K64407US



### Each information

Depth	1.38"
Width	18"
Height	7.32"
Gross weight	1.75lbs
UPC#	085896644071
Unit quantity	1

### Case information

Depth	18.62"
Width	7.31"
Height	8.5"
Gross weight	9.60lbs
UPC#	50085896644076
Unit quantity	5

### Shipping Information

Country of origin	CN
Minimum Order Quantity	5
Warranty Period	36
Lowest possible unit	Case

### General information

Color	Black
Moore #	KMW64407US
Layer/Pallet	5
Cases/Layer	12

### Product Description

With more than 30 years of expertise designing peripherals for busy professionals, Kensington's Pro Fit Washable Keyboard is perfect for environments like schools or healthcare facilities. Whether you want to avoid damage caused by spilled coffee, soda or water, or you want to safely clean off germs and bacteria without damaging the internal components, this is the keyboard for you. With a rugged design that can also withstand drops and bumps, the keyboard can be immersed in water or sprayed under the faucet to get it completely clean.

### Features

- Rugged waterproof and washable design resists spills and makes cleaning easy
- Can safely stand up to immersion or frequent use of spray cleaners (USB connector cannot get wet)
- Wired, reliable USB connectivity without the need for batteries
- Built to last with a limited lifetime warranty
- Full-size 104-key layout
- Compatible with Windows 10, 8.1, 8, 7 and Mac OS X 10.6 and later
- Black keyboard with 104-key layout
- Do not immerse the USB plug

### Specifications

- **Color** Black
- **Compatibility** Windows 8, Vista, Windows 7, XP, Windows 10, Mac OS X 10.11, Mac OS X 10.10, Mac OS 10.9
- **Keyboard Features** Soft Touch
- **Protection** Antimicrobial