

Pro Fit® Full-Size Wireless Mouse

72370



Product Description

The Kensington Pro Fit® Full-Size Wireless Mouse has an ergonomic, right-handed shape with a soft rubber grip for all-day comfort. It features a high-definition optical sensor with a pointer speed quick-select button for enhanced productivity. It uses 2.4 GHz wireless for long range with minimal interference. And it is built to last with a limited lifetime warranty. PC and Mac compatible.

Features

- Ergonomic, right-handed shape with soft rubber grip
- Pointer speed quick-select button
- Forward/back buttons
- High-definition optical sensor (up to 1200 DPI) for responsive control
- 2.4 GHz wireless for long range and minimal interference
- Plug and Play - no drivers required
- Scroll wheel with middle button
- Built to last with a limited lifetime warranty

Specifications

- **Colour** Black
- **USB Receiver Size** Standard
- **Compatibility** Windows 8, Windows 10, Mac OS X 10.11, Mac OS X 10.10, Chrome OS 44 and above, Mac OS 10.9, Vista, Windows 7, XP
- **Wireless Type** 2.4Ghz
- **Controls** Navigation Buttons, DPI Adjustment, Scrollwheel
- **Sensor** Optical

Product information

Depth	120mm
Width	78mm
Height	40mm
Gross weight	0.27kg

Retail Packaging Information

Depth	180mm
Width	155mm
Height	78mm
Gross weight	0.27kg
UPC#	5028252305082
Unit quantity	1

Master Case Information

Depth	390mm
Width	180mm
Height	230mm
Gross weight	1.57kg
UPC#	5028252305099
Unit quantity	4

Shipping Information

Minimum Order Quantity	4
Warranty Period	99