

6 Liter Class K Wet Chemical Fire Extinguisher

Part number 25074

Cooking media

Rechargeable

UL Rated K



Description

Suitable for use on Class K cooking grease and oil fires.

The move toward more efficient cooking appliances and the widespread use of unsaturated cooking oils dictates the development and use of new types of portable fire extinguishers.

These wet chemical extinguishers are designed to deliver the agent safely on to the fire with a more gentle application. In addition the fire fighting agent has a greater fire fighting capacity and cooling effect on grease fires than dry chemical agents.

Features

- Safe and durable stainless steel cylinder
- Clear instruction label using graphics to show steps required to operate extinguisher
- Easy-to-pull safety pin
- Tough impact resistant metal valve, handle & lever
- 6 liter (1.6 gallons) of fire extinguishing agent (Average)
- 6 year limited warranty
- UL approved wall hanger
- Corrosion resistant cylinder & valve assembly

"Shipped Factory Filled"

For use on the following type of fire:



At a Glance

- Model WC-100 KS Pro
- Wet chemical
- UL listed
- UL rated K
- Potassium Acetate
- Supplied with wall hanger
- 6 year limited warranty

Pt # 25074 - 1 pack
UPC: Not Available
I2F: Not Available

Product Specification

Net agent weight (Average)	1.6 gallons (6 liters)
Unit weight (Average)	23.3 lb.
Diameter	7.0 inches
Height	19.5 inches
Discharge time	55-60 seconds
Discharge range	8-12 feet
Operating pressure	100 psi
Cylinder	Stainless steel
Valve, handle, lever	Brass & stainless steel

Packaging Options



SHIPPED IN CARTON

Packaging dimensions (inches)

	Depth	Width	Height
Carton	8.19	8.19	26.37