

Pro 20 CD Fire Extinguisher

Part number 466183

Electrical risks

Rechargeable

UL Rated 10-B:C



Description

Suitable for use on Class B (liquids) and Class C fires (energized electrical equipment).

The Pro 20 carbon dioxide unit is environmentally safe and ideal for protecting delicate electronic equipment as the clean agent leaves no residue. The cylinder is manufactured from aluminum and the valve assembly is metal.

Features

- Clear instruction label using graphics to show steps required to operate extinguisher
- Easy-to-pull safety pin
- Tough impact resistant metal valve, handle & lever
- 20 lb. of fire extinguishing agent (Average)
- 5 year limited warranty
- UL approved wall hanger
- Powder coated cylinder for corrosion protection

At a Glance

- Model Pro 20 CD M-4
- Carbon dioxide
- UL listed
- UL rated 10-B:C
- Supplied with wall hanger
- 5 year limited warranty
- Suitable for use on energized electrical equipment

For use on the following types of fire:



Pt # 466183 - 1 pack
 UPC: 0-47871-66183-1
 I2F - 20047871661835

Product Specification

Net agent weight (Average)	20 lb.
Unit weight (Average)	51.0 lb.
Diameter	8.0 inches
Height	26.0 inches
Discharge time	15-17 seconds
Discharge range	3-8 feet
Operating pressure	850 psi
Cylinder	Aluminum
Valve, handle, lever	Brass & stainless steel
Strap Bracket (not supplied)	U.S.C.G approved

Packaging Options



SHIPPED IN CARTON

Packaging dimensions (inches)

	Depth	Width	Height
Carton	8.0	13.0	28.75