

Thermo Scientific Cimarec Basic hot plates, stirrers and stirring hot plates combine unsurpassed performance with a sleek, rugged design.

## Thermo Scientific Cimarec Basic

Hot Plates, Stirrers and Stirring Hot Plates

### Features:

- Choose from 4" x 4" (10.2 x 10.2 cm) or 7" x 7" (17.8 x 17.8 cm) top plate sizes.
- New top plate design reduces chance of breakage.
- Updated body directs spills away from internal components.
- Fast heating time - unit reaches maximum temperature in under eight minutes.
- Solid ceramic top plate is easily cleaned and resistant to acid and alkali.
- Rugged cast aluminum body provides stability and durability.
- Adjustable stirring speed range from 100 to 1200 rpm.
- Stirring models include a TFE-coated stir bar.
- Integral ring-stand holder accommodates 0.5" (1.3 cm) diameter support rod.
- All models come with a 24 month warranty.



## Thermo Scientific Cimarec Basic Specifications and Ordering Information

Part No.	Description	Surface Type	Volts	Amps	Watts	Operating Temperature Range °C (°F)	Stir Range RPM	Shipping Weight lb. (kg)
<b>4" x 4" Cimarec™ Basic</b>								
<i>Heating Surface: 4.25" x 4.25" (10.8 x 10.8 cm) Overall Dimensions: 5.7" W x 7.9" D x 5.0" H (14.5 x 20 x 12.7 cm)</i>								
S194615	Stirrer	Ceramic top	120	0.45	21	NA	100-1200	4.4 (2)
HP194515	Hot plate	Ceramic top	120	3.21	385	150-538 (302-1000)	NA	3.4 (1.5)
SP194715	Stirring hot plate	Ceramic top	120	3.45	405	150-538 (302-1000)	100-1200	4.9 (2.2)
<b>7" x 7" Cimarec Basic</b>								
<i>Heating Surface: 7.25" x 7.25" (18.4 x 18.4 cm) Overall Dimensions: 8.3" W x 11.1" D x 5.0" H (21.1 x 28.2 x 12.7 cm)</i>								
S194925	Stirrer	Ceramic top	120	0.48	23	NA	100-1200	7 (3.2)
HP194825	Hot plate	Ceramic top	120	8.96	1062	150-538 (302-1000)	NA	6.1 (2.8)
SP195025	Stirring hot plate	Ceramic top	120	9.18	1086	150-538 (302-1000)	100-1200	7.7 (3.5)



© 2009 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representative for details.

**North America:** USA/Canada +1 800 553 0039

[www.thermo.com/hotplates](http://www.thermo.com/hotplates)

Europe: Austria +43 1 801 40 0, Belgium +32 2 482 30 30, France +33 2 2803 2180, Germany national toll free 08001-536 376, Germany international +49 6184 90 6940, Italy +39 02 02 95059 434-254-375, Netherlands +31 76 571 4440, Nordic/Baltic countries +358 9 329 100, Russia/CIS +7 (812) 703 42 15, Spain/Portugal +34 93 223 09 18, Switzerland +41 44 454 12 12, UK/Ireland +44 870 609 9203

**Asia:** China +86 21 6885 4588 or +86 10 8419 3588, India toll free 1800 22 8374, India +91 22 6716 2200, Japan +81 45 453 9220,

**Other Asian countries** +852 2885 4613 Countries not listed: +49 6184 90 6940 or +33 2 2803 2180