

TouchNTuff®

ADVANCED PRODUCT & WORKER PROTECTION

92-575 / 92-675

Powdered and Powder-Free
Disposable Nitrile Glove



Nitrile

Robust nitrile glove proven for food safety and general applications

- Superior chemical splash protection*
- Soft, durable nitrile material for added comfort
- Textured fingertips provide reliable grip
- Complies with FDA food handling requirements



Industries

- Agriculture
- Automotive
- Chemical and petrochemical
- Distribution
- Food processing
- General industry
- Machinery and equipment
- Pharmaceutical, life sciences
- Research laboratories

Applications

- Assembly and inspection
- Chemical handling
- Food handling and processing
- Laboratory analysis
- Light assembly tasks
- Maintenance
- Transferring liquids and solids

TECHNICAL DATA SHEET: PRODUCT INFORMATION:

Product	92-575	92-675
Material	Nitrile	
Color	Dark Blue	
Glove Design	Ambidextrous, Powdered, Textured Grip	Ambidextrous, Powder Free, Textured Grip
Cuff	Beaded Cuff	
Manufacturing/ QMS Audit Standards	ISO 9001	
Regulatory/Standards Compliance	EN 420, EN 374/1,2,3, ASTM D6319, FDA 21 CFR 177-2600, Compliant with U.S. Food Contact Regulations, Arrete 09/11/04, European Regulation 1935/2004, German Recommendation for Food Commodities	
Packaging	100 gloves per dispensers, 10 dispensers per shipper carton, 1000 gloves per shipper cartons.	
Storage	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.	
Country of Origin	Thailand	Malaysia / Thailand
User Needs Segment	Robust Glove - Gloves that provide added strength, durability and chemical splash protection for longer wear times.	

PHYSICAL PROPERTIES:

PROPERTY	SIZE	TYPICAL VALUES				TESTING METHOD
		S 6½-7	M 7½-8	L 8½-9	XL 9½-10	
Length (mm/in)	92-575	240/9.5	240/9.5	240/9.5	240/9.5	ASTM D3767/EN 420
	92-675	240/9.5	240/9.5	240/9.5	240/9.5	
Average Palm Width (mm/in)		85/3.35	95/3.74	105/4.13	111/4.37	

Freedom from Holes (Inspection level I)	92-575	1.5 AQL	ASTM D5151/EN 374-2
	92-675	4.0 AQL	
Palm Thickness Single Wall	mm: 0.11 / mil: 4.3		ASTM D3767/EN 420

	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength	> 14 Mpa	> 14 Mpa	ASTM D 412-06a
Elongation at Break (%)	> 500	> 400	ASTM D 412-06a
Force at break (N)	> 6	> 6	EN 455-2

ORDERING INFORMATION:

	SIZE	S 6½-7	M 7½-8	L 8½-9	XL 9½-10
92-575	ASPEN	586193	586194	586195	586196
	ORACLE	105125	105126	105127	105128
92-675	ASPEN	565716	565717	565718	565719
	ORACLE	105081	105082	105083	105084

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

*Warning: No glove provides complete protection against all chemicals. Users must test the gloves against the particular chemicals and environment in which they will be used.

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa
Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 2 528 74 00
F: +32 2 528 74 01

Asia Pacific
Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
63000 Cyberjaya
Selangor, Malaysia
T: +60 3 8310 6688
F: +60 3 8318 6699

North America
Ansell Healthcare Products LLC
111 Wood Avenue South
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean
Ansell Brazil Ltda.
Rua das Figueiras 474 - 4º Andar
Bairro Jardim
SP 09080-300 Santo André
Brazil
CNPJ: 03.496.778/0001-21
+55 11 3356 3100

Australia
Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Russia
Анселл РУС
123610 Россия, Москва
Краснопресненская
Наб. 12, п.3, оф. 1304А
Тел. +7 495 258 13 16

Regulatory Compliance

CE 0493

Performance Standards

