




4700 W. 160th St.
Cleveland, OH 44135
PH:800-321-9532
FX:800-321-9535
www.oatey.com

TECHNICAL SPECIFICATION

**LEVEL FIT
ADJUSTABLE
CLOSET FLANGE WITH PLASTIC
RING, LONG MOUNTING SLOTS**



TECHNICAL SPECIFICATION: Oatey Level Fit Adjustable Closet Flanges are designed with four countersunk holes for secure attachment to the floor. Radial slots extend 130 degrees to allow exact alignment of the water closet. All plastic flange solvent welds inside of 4", or over 3" Schedule 40 DWV pipe.



APPROVALS AND LISTINGS



IAPMO Listed

PHYSICAL/CHEMICAL PROPERTIES

Material/Color ABS Plastic = Black
 PVC Plastic = White

DIRECTIONS FOR USE

Punch 1-3/8" hole in metal stud. Snap clamp into hole. Clamp is offset to allow for adjustment of centers from stud to stud. 1/2" clamp allows for 1/4" and 3/8" tubing installation through secondary holes in clamp. Check with local codes to ensure proper spacing requirements for piping support.

PRECAUTIONS

Read cautions and directions on packaging carefully before using this product. KEEP OUT OF REACH OF CHILDREN.

COMMON APPLICATIONS

Oatey Metal Stud Insulating Pipe Clamps can be installed to isolate piping away from the stud and reduce water line noise and vibration in metal stud installations.

Consult Oatey Technical Department for applications not specifically referenced above.

PRODUCT NUMBER	DESCRIPTION	PACK	CARTON WEIGHT
43510	3"or 4" ABS adjustable closet flange	12	7lbs
43511	3"or 4" PVC adjustable closet flange	12	7lbs
43526	3"or 4" ABS adjustable flange w/test cap	6	7lbs
43527	3"or 4" PVC adjustable flange w/test cap	6	7lbs