



4700 W. 160th St.
Cleveland, Ohio 44135
Ph: (800) 321-9532
Fax: (800) 321-9535
www.oatey.com



74000 Series PVC Adjustable General Purpose Cleanout PVC Barrel With 6" Round Cover With Round Ring



SUBMITTAL SPECIFICATION

Engineering Specification: Oatey adjustable general purpose cleanouts are used for general service in restaurants, restrooms and other commercial applications where traffic is expected. Barrel assembly is completely adjustable to meet the finished floor height.

Job Reference



(All dimensions in inches)

- Barrel diameter is 3-1/2 in. IPS thread.
- Primer tap knock-out is 1/2 in. FIP thread.

✓	Socket Size (C)	Base Material	Cover Finish	Part Number
	3 or 4 in. Pipe Fit	PVC	Brass	74137
	3 or 4 in. Pipe Fit	PVC	Nickel	74167
	3 or 4 in. Pipe Fit	PVC	Chrome	74197
	4 in. Pipe Fit	PVC	Brass	74138
	4 in. Pipe Fit	PVC	Nickel	74168
	4 in. Pipe Fit	PVC	Chrome	74198
	4 in. Hub Fit	PVC	Brass	74139
	4 in. Hub Fit	PVC	Nickel	74169
	4 in. Hub Fit	PVC	Chrome	74199

	Dimensional Data		
	A	B	C
3 in.	4.75 in.	1.25 – 2.75 in.	3 in. Hub, 4 in. Pipe
4 in.	5.00 in.	1.25 – 2.75 in.	4 in. Pipe
4 in.	2.00 in.	1.25 – 2.75 in.	4 in. Hub

*3 in. plug included in barrel.

Cover Properties	
Finish	Load*
Brass	Medium
Nickel	Medium
Chrome	Medium

*Load is defined by ASME A112.21.1M.
Light Duty – Safe live load under 2000 lbs.
Medium Duty – Safe live load between 2000 lbs. and 4999 lbs.



4700 W. 160th St.
Cleveland, Ohio 44135
Ph: (800) 321-9532
Fax: (800) 321-9535
www.oatey.com



84000 Series ABS Adjustable General Purpose Cleanout PVC Barrel With 6" Round Cover With Round Ring



SUBMITTAL SPECIFICATION

Engineering Specification: Oatey adjustable general purpose cleanouts are used for general service in restaurants, restrooms and other commercial applications where traffic is expected. Barrel assembly is completely adjustable to meet the finished floor height.

Job Reference



(All dimensions in inches)

- Barrel diameter is 3-1/2 in. IPS thread.
- Primer tap knock-out is 1/2 in. FIP thread.

✓	Socket Size (C)	Base Material	Cover Finish	Part Number
	3 or 4 in. Pipe Fit	ABS	Brass	84137
	3 or 4 in. Pipe Fit	ABS	Nickel	84167
	3 or 4 in. Pipe Fit	ABS	Chrome	84197
	4 in. Pipe Fit	ABS	Brass	84138
	4 in. Pipe Fit	ABS	Nickel	84168
	4 in. Pipe Fit	ABS	Chrome	84198
	4 in. Hub Fit	ABS	Brass	84139
	4 in. Hub Fit	ABS	Nickel	84169
	4 in. Hub Fit	ABS	Chrome	84199

	Dimensional Data		
	A	B	C
3 in.	4.75 in.	1.25 – 2.75 in.	3 in. Hub, 4 in. Pipe
4 in.	5.00 in.	1.25 – 2.75 in.	4 in. Pipe
4 in.	2.00 in.	1.25 – 2.75 in.	4 in. Hub

*3 in. plug included in barrel.

Cover Properties	
Finish	Load*
Brass	Medium
Nickel	Medium
Chrome	Medium

*Load is defined by ASME A112.21.1M.

Light Duty – Safe live load under 2000 lbs.

Medium Duty – Safe live load between 2000 lbs. and 4999 lbs.