



4700 W. 160th St.
Cleveland, Ohio 44135
Ph: (800) 321-9532
Fax: (800) 321-9535
www.oatey.com



74000 Series PVC Adjustable General Purpose Cleanout PVC Barrel With 6" Round Cover With Square Ring



SUBMITTAL SPECIFICATION

Engineering Specification: Oatey adjustable general purpose cleanouts are used for general service in restaurants, restrooms and other commercial applications where traffic is expected. Barrel assembly is completely adjustable to meet the finished floor height.

Job Reference



(All dimensions in inches)

- Barrel diameter is 3-1/2 in. IPS thread.
- Primer tap knock-out is 1/2 in. FIP thread.

| ✓ | Socket Size (C) | Base Material | Cover Finish | Part Number |
|---|---------------------|---------------|--------------|-------------|
| | 3 or 4 in. Pipe Fit | PVC | Brass | 74147 |
| | 3 or 4 in. Pipe Fit | PVC | Nickel | 74177 |
| | 3 or 4 in. Pipe Fit | PVC | Chrome | 74207 |
| | 4 in. Pipe Fit | PVC | Brass | 74148 |
| | 4 in. Pipe Fit | PVC | Nickel | 74178 |
| | 4 in. Pipe Fit | PVC | Chrome | 74208 |
| | 4 in. Hub Fit | PVC | Brass | 74149 |
| | 4 in. Hub Fit | PVC | Nickel | 74179 |
| | 4 in. Hub Fit | PVC | Chrome | 74209 |

| | Dimensional Data | | |
|-------|------------------|-----------------|-----------------------|
| | A | B | C |
| 3 in. | 4.75 in. | 1.25 – 2.75 in. | 3 in. Hub, 4 in. Pipe |
| 4 in. | 5.00 in. | 1.25 – 2.75 in. | 4 in. Pipe |
| 4 in. | 2.00 in. | 1.25 – 2.75 in. | 4 in. Hub |

*3 in. plug included in barrel.

| Cover Properties | |
|------------------|--------|
| Finish | Load* |
| Brass | Medium |
| Nickel | Medium |
| Chrome | Medium |

*Load is defined by ASME A112.21.1M.
Light Duty – Safe live load under 2000 lbs.
Medium Duty – Safe live load between 2000 lbs. and 4999 lbs.



4700 W. 160th St.
Cleveland, Ohio 44135
Ph: (800) 321-9532
Fax: (800) 321-9535
www.oatey.com

84000 Series



ABS Adjustable General Purpose Cleanout PVC Barrel With 6" Round Cover With Square Ring



SUBMITTAL SPECIFICATION

Engineering Specification: Oatey adjustable general purpose cleanouts are used for general service in restaurants, restrooms and other commercial applications where traffic is expected. Barrel assembly is completely adjustable to meet the finished floor height.

Job Reference



(All dimensions in inches)

- Barrel diameter is 3-1/2 in. IPS thread.
- Primer tap knock-out is 1/2 in. FIP thread.

| ✓ | Socket Size (C) | Base Material | Cover Finish | Part Number |
|---|---------------------|---------------|--------------|-------------|
| | 3 or 4 in. Pipe Fit | ABS | Brass | 84147 |
| | 3 or 4 in. Pipe Fit | ABS | Nickel | 84177 |
| | 3 or 4 in. Pipe Fit | ABS | Chrome | 84207 |
| | 4 in. Pipe Fit | ABS | Brass | 84148 |
| | 4 in. Pipe Fit | ABS | Nickel | 84178 |
| | 4 in. Pipe Fit | ABS | Chrome | 84208 |
| | 4 in. Hub Fit | ABS | Brass | 84149 |
| | 4 in. Hub Fit | ABS | Nickel | 84179 |
| | 4 in. Hub Fit | ABS | Chrome | 84209 |

| | Dimensional Data | | |
|-------|------------------|-----------------|-----------------------|
| | A | B | C |
| 3 in. | 4.75 in. | 1.25 – 2.75 in. | 3 in. Hub, 4 in. Pipe |
| 4 in. | 5.00 in. | 1.25 – 2.75 in. | 4 in. Pipe |
| 4 in. | 2.00 in. | 1.25 – 2.75 in. | 4 in. Hub |

*3 in. plug included in barrel.

| Cover Properties | |
|------------------|--------|
| Finish | Load* |
| Brass | Medium |
| Nickel | Medium |
| Chrome | Medium |

*Load is defined by ASME A112.21.1M.

Light Duty – Safe live load under 2000 lbs.

Medium Duty – Safe live load between 2000 lbs. and 4999 lbs.