

Tube Rollers

Our tube rollers provide a gentle and highly efficient rocking and rolling motions, ideal for mixing blood samples, viscous substances and liquid-solid suspensions. Used in a variety applications, prevention of blood coagulation and immune precipitation etc.

MX-T6-S Classic Tube Roller

Features:

- Rocking and rolling motion for complete mixing
- Speed range of 0-70rpm
- Six roller design with small footprint and easy cleaning
- Designed for continuous operation



MX-T6-S

MX-T6-Pro LCD Digital Tube Roller

Features:

- Rocking and rolling motion for complete mixing
- LCD display the speed and time
- Speed range of 10-70rpm
- Six roller design with small footprint and easy clean
- Designed for continuous or timed operation



Mixers, Rotators and Rollers

Specifications

	MX-T6-Pro	MX-T6-S
Voltage [VAC]	100-240	100-240
Frequency [Hz]	50/60	50/60
Power [W]	30	25
Motor type	DC motor	DC motor
Rocking motion	Rocking and rolling	Rocking and rolling
Amplitude [mm]	24	24
Max. load capacity [kg]	4	4
Number of rollers	6	6
Roller size (L) [mm]	280	280
Speed range [rpm]	10 -70	0-70
Speed display	LCD	Scale
Timer	Yes	-
Timer display	LCD	-
Time setting range [min]	1-1199	-
Operation type	Continuous / timed operation	Continuous operation
Dimensions [DxWxH mm]	450x260x120	450x260x120
Weight [kg]	5.1	4.5
Permissible ambient temperature [°C]	5-40	5-40
Permissible relative humidity	80%	80%
Protection class acc. To DIN EN60529	IP21	IP21

