









































Model/ Cat . No.:	Stator	Rotor	Shaft	Application Field/Industry	Medium Function	Treatable Volume (H2O)/ml	Tool length (mm)	Min/max emersion depth (mm)	Max viscosity (mPa)	Ultimate suspension fitness (µm)	Ultimate Emulsion fitness (µm)
S20C/SR20  <b>18900118/ 18900123</b>	 20mm	 15mm		Ceramic Pharmaceutical Petrochemistry Sewage Control	SOLID / LIQUID	10-5000	220	40/175	10,000	10-50	1-10
S20C/CR20  <b>18900118/ 18900125</b>	 20mm	 15mm		Paper&Tissue Food Tobacco Medicine Sewage Control	STRINGY/ FIBROUS	10-5000	220	40/175	30,000	10-50	1-10
S20C/MR20  <b>18900118/ 18900127</b>	 20mm	 15mm		Ceramic Paint	SOLID / LIQUID	10-5000	220	40/175	10,000	10-50	1-10
S20F/ER20  <b>18900119/ 18900129</b>	 20mm	 15mm		Paper & Tissue Pharmaceutical Sewage Control Paint	SUSPENSION/ EMULSIONS	10-5000	220	40/175	10,000	10-50	1-10
S20F/CR20  <b>18900119/ 18900125</b>	 20mm	 15mm		Biotechnology Paper & Tissue Food Tobacco Medicine Sewage Control	STRINGY/ FIBROUS	10-5000	220	40/175	10,000	10-150	1-10

**Generator/Rotor Matching & Application Table**

Model/ Cat . No.:	Stator	Rotor	Shaft	Application Field/Industry	Medium Function	Treatable Volume (H2O)/ml	Tool length (mm)	Min/max emersion depth (mm)	Max viscosity (mPa)	Ultimate suspension fitness (µm)	Ultimate Emulsion fitness (µm)
S20F/MR20  <b>18900119/ 18900127</b>	 20mm	 15mm		Ceramic Paper & Tissue Food Cosmetics Petrochemistry Paint	SOLID / LIQUID	10-5000	220	40/175	10,000	10-150	1-10
S30C/SR30  <b>18900120/ 18900124</b>	 30mm	 23mm		Paper & Tissue Food Pharmaceutical Medicine Sewage Control	SOLID / LIQUID	100-8000	220	40/175	10,000	5-25	1-5
S30C/CR30  <b>18900120/ 18900126</b>	 30mm	 23mm		Paper & Tissue Food Pharmaceutical Medicine Sewage Control	STRINGY/ FIBROUS	100-8000	220	40/175	30,000	5-25	1-5
S30C/MR30  <b>18900120/ 18900128</b>	 30mm	 23mm		Ceramic Paint	SOLID / LIQUID	100-8000	220	40/175	10,000	5-25	1-5

**Generator/Rotor Matching & Application Table**

Model/ Cat . No.:	Stator	Rotor	Shaft	Application Field/Industry	Medium Function	Treatable Volume (H2O)/ml	Tool length (mm)	Min/max emersion depth (mm)	Max viscosity (mPa)	Ultimate suspension fitness (µm)	Ultimate Emulsion fitness (µm)
S30C/MR20 <b>18900120/ 18900127</b>	 30mm	 15mm		Ceramic Food Sewage Control	MIXING / STIRRING	250-20,000	220	40/175	10,000	HIGH SPEED MIXER	
S30F/ER30 <b>18900121/ 18900130</b>	 30mm	 23mm		Paper & Tissue Pharmaceutical Sewage Control Paint	SUSPENSION/ EMULSIONS	100-8000	220	40/175	10,000	5-25	1-5
S30F/SR30 <b>18900121/ 18900124</b>	 30mm	 23mm		Paper & Tissue Pharmaceutical Sewage Control Paint	SOLID / LIQUID	100-8000	220	40/175	10,000	5-25	1-5
S30F/MR30 <b>18900121/ 18900128</b>	 30mm	 23mm		Ceramic Food Cosmetics Pharmaceutical Tobacco	SOLID / LIQUID	100-8000	220	40/175	10,000	5-25	1-5
S40C/MR30 <b>18900122/ 18900128</b>	 40mm	 23mm		Ceramic Food Sewage Control	MIXING / STIRRING	1000-40,000	220	40/175	10,000	HIGH SPEED MIXER	

