

MicroPette Digital Micro-Pipettors



Simply turn the plunger button
for volume selection

Finger support keeps the instrument
in place with minimum user effort

Tip ejector allows
convenient one-handed operation



Carousel Pipettor Stand




Linear Pipettor Stand



Ejector collar and tip cone
can be removed

Durable tip cone materials
provide excellent chemical resistance



Features

- Lightweight, ergonomic, low force design
- Digital display clearly reads volume setting
- The range of pipettors cover a volume range from 0.1ul to 5000ul
- Easy to calibrate and maintain with tool supplied
- Manufactured from modern innovative materials
- Individual piston/tip cone assemblies allow easy repair and maintenance
- Compound material tip cone design allows visual seal verification
- Can be used with 'universal' style pipette tips.
- Calibrated in accordance with ISO/DIS 8655. Each pipettor supplied with individual test certificate.
- **1 YEAR WARRANTY**

MicroPette Variable Volume Single Channel Manual Pipettors

Cat No.	Vol, µl	Incr, µl	Test Vol, µl	Accuracy, (±%)	Precision, (±%)
71211101	0.1-2.5	0.05	2.5/1.25/0.25	2.5/3.00/12.0	2.00/3.00/6.00
71211104	0.5-10	0.1	10/5/1	1.00/1.50/2.50	0.80/1.50/1.50
71211105	2-20	0.5	20/10/2	0.90/1.20/3.00	0.40/1.00/2.00
71211106	5-50	0.5	50/25/5	0.60/0.90/2.00	0.30/0.60/2.00
71211108	10-100	1.0	100/50/10	0.80/1.00/3.00	0.15/0.40/1.50
71211109	20-200	1.0	200/100/20	0.60/0.80/3.00	0.15/0.30/1.00
71211114	100-1000	5.0	1000/500/100	0.60/0.70/2.00	0.20/0.25/0.70
71211117	1000-5000	50.0	5000/2500/1000	0.50/0.60/0.70	0.15/0.30/0.30
71211133	2000-10000	100.0	10000/5000/2000	0.60/1.20/3.00	0.20/0.30/0.60

MicroPette Variable Volume 8 - Channel Manual Pipettors

Cat No.	Vol, µl	Incr, µl	Test Vol, µl	Accuracy, (±%)	Precision, (±%)
71211204	0.5-10	0.1	10/5/1	1.50/2.50/4.00	1.50/2.50/4.00
71211206	5-50	0.5	50/25/5	1.00/1.50/3.00	0.50/1.00/2.00
71211212	50-300	5.0	300/150/50	0.70/1.00/1.50	0.25/0.50/0.80

MicroPette Variable Volume 12 - Channel Manual Pipettors

Cat No.	Vol, µl	Incr, µl	Test Vol, µl	Accuracy, (±%)	Precision, (±%)
71211304	0.5-10	0.1	10/5/1	1.50/2.50/4.00	1.50/2.50/4.00
71211306	5-50	0.5	50/25/5	1.00/1.50/3.00	0.50/1.00/2.00
71211312	50-300	5.0	300/150/50	0.70/1.00/1.50	0.25/0.50/0.80

MicroPette Fixed Volume Single Channel Manual Pipettors

Cat No.	Vol, µl	Test Vol, µl	Accuracy, (±%)	Precision, (±%)
71212118	5	5	1.3	1.2
71212119	10	10	0.8	0.8
71212120	20	20	0.6	0.5
71212121	25	25	0.5	0.3
71212122	50	50	0.5	0.3
71212123	100	100	0.5	0.3
71212124	200	200	0.4	0.2
71212125	250	250	0.4	0.2
71212126	500	500	0.3	0.2
71212127	1000	1000	0.3	0.2
71212128	2000	2000	0.3	0.15
71212129	5000	5000	0.3	0.15

Accessories

Description

71000085	Linear Pipettor Stand, holds up to 6 pipettors
71000084	Carousel Pipettor Stand, holds up to 6 pipettors



8-Channel 50-300ul