


Day/Night Weather Resistant Color Bullet Camera / 63 IR LEDs

VL7038K 2.8-12mm auto iris varifocal lens, dark grey housing

Features

- 1/3" 1.3MP Sony Sensor
- 1000 TV lines of resolution
- True Day/Night compatibility
- Multi-mount is a unique mount allowing installers to manipulate the camera to almost every angle with simplicity
- Zero noise and no ghosting effect with digital noise reduction (DNR)
- External control rings for easy focus & distance adjustment
- Highest resolution: vivid, sharp picture in complete darkness
- 5 year warranty



Specifications

Image Sensor	1/3" 1.3MP Sony Sensor
Resolution.....	1000 TV lines
Minimum Illumination.....	0 lux (IR LED on)
Effective Pixels	1305 (H) x 1049 (V)
Total Pixels	1312 (H) x 1069 (V)
Number of IR LEDs	63
IR Range	164 ft. (depending on scene reflection)
IR LED Wavelength	850nm
White Balance	ATW / AWB / AWC-Set / Manual
S/N Ratio	More than 50dB (AGC off, weight on)
Backlight Compensation.....	HLC / BLC / Off / WDR
Electronic Shutter Speed.....	Auto / Manual / Flicker
OSD.....	Available
DNR.....	On / Off (level adjustable)
DWDR	On / Off
Sharpness	0-10' (level adjustable)
Privacy.....	On / Off (16 zones)
Scanning System.....	Progressive scan
Brightness.....	0-20 (level adjustable)

Synchronization.....	Internal
Day/Night.....	Color / BW / Auto / EXT
Motion Detection.....	On / Off (4 zones)
Sense-Up.....	Off / Auto
Mirror	On / Off
Digital Zoom	On (1x - 8x) / Off
Power Consumption	12VDC, 200mA (CDS off) 700mA (CDS on) 24VAC, 150mA (CDS off) 450mA (CDS on)
Power Supply	12VDC / 24VAC dual voltage operation (power supply not included)
Operating Temperature/	
Humidity.....	- 4°F – 140°F / RH 95% max.
Storage Temperature/	
Humidity.....	- 4°F – 140°F / RH 95% max.
Dimensions.....	5.31" (W) x 3.74" (H) x 11.57" (L)
Weight	4 lbs.

Optional Accessories



INTJBS
Square
Junction Box



INTCM
Corner/Pole
Adaptor



PSW4
24VAC
Power Supply



PSW5
12VDC
Power Supply



Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 7/1/15