

FFAR10-FS24LSTACKMED2



78.75" x 24" x 23.5" (H x W x D)

Stacked combination of FFAR10MED2 auto defrost all-refrigerator and FS24LMED2 compact manual defrost all-freezer, both with locks, digital controls, and NIST calibrated alarm/thermometers

Highlights:

Specially designed and featured to meet the CDC and VFC's guidelines for safe vaccine storage

Independent refrigerator and freezer storage in one slim-fitting footprint for space-challenged facilities

User-friendly front control panel keeps the thermostat and alarm in reach without having to open the door

Product Features:

Space-saving design	Allows you to create a full refrigerator-freezer with independent controls in a slim-fitting footprint
Meets CDC & VFC guidelines	Designed to comply with the most current guidelines for vaccine storage
FFAR10MED2 all-refrigerator	10.1 cu.ft. auto defrost all-refrigerator with digital controls, internal fan, flat door liner, and adjustable shelving
FS24LMED2 all-freezer	Compact manual defrost all-freezer with digital thermostat and wire shelving
Easy assembly	Unit ships in three boxes for customer to install the StackRack on the bottom refrigerator/freezer and place and secure the other unit on top
Access ports	Rear-mounted 3/8" access port in both units allows users to install their own monitoring equipment
High/low temperature alarms	Audible alarm sounds if the interior temperature rises or falls out of set range
NIST calibrated temperature display	Alarms include continuous NIST calibrated display of the current interior and high/low temperature, and can be switched from Celsius to Fahrenheit at the touch of a button
Buffered temperature probes	Thermometer probe is encased in a glycol-filled bottle and stored in a fixed box on the center shelf. This is the ideal way to produce temperature readings closest to stored contents, as recommended by the CDC and VFC's guidelines

FFAR10-FS24LSTACKMED2 Specifications:

Overview	
Height of Cabinet	78.75" (200 cm)
Width	24.0" (61 cm)
Depth	23.5" (60 cm)
Depth with Handle	24.75" (63 cm)
Depth with door at 90°	45.5" (116 cm)
Capacity	11.5 cu.ft. (326 L)
Door	White
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Voltage/Frequency	115 V AC/60 Hz
Parts & Labor Warranty	2 Years
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Factory Reversible
Adjustable Shelves	Yes
Interior Light	Yes
Refrigerator - Interior Height	48.25" (123 cm)
Refrigerator - Interior Width	20.5" (52 cm)
Refrigerator - Interior Depth	17.75" (45 cm)
Refrigerator - Capacity	10.1 cu.ft
Refrigerator - Shelf Type	Wire
Refrigerator - Shelf Qty	4
Refrigerator - Temperature Range	2°C to 8°C
Refrigerator - Refrigerant Type	R134a
Refrigerator - Refrigerant Amount	3.0 oz.
Freezer - Interior Height	14.38" (37 cm)
Freezer - Interior Width	13.5" (34 cm)
Freezer - Interior Depth	13.25" (34 cm)
Freezer - Capacity	1.4 cu.ft
Freezer - Shelf Type	Wire
Freezer - Shelf Qty	1
Thermostat Type	Digital

Fan Type
Freezer - Temperature Range
Freezer - Refrigerant Type
Freezer - Refrigerant Amount

