

FS24LMED



20" x 18.5" x 17.63" (H x W x D)

Compact all-freezer capable of -20° C degree operation, with lock, alarm with temperature display, and hospital grade cord

Highlights:

Compact size for easy placement above counters

Factory installed lock provides security you can count on

High temperature alarm includes external NIST calibrated temperature readout

Product Features:

Compact dimensions	Ideal size for use on top of counters
-20° capable	Low temperature capability ideal for certain sensitive items
Factory installed lock	Keyed lock for secure interior
High temperature alarm	Warns of temperature fluctuations and includes an external temperature readout on the door
NIST calibrated temperature display	Alarm includes NIST calibrated display of the current interior and high/low temperature
Hospital grade cord with 'green dot' plug	Secure three-pronged cord for added unit safety
Manual defrost	Static cooling system for reduced temperature fluctuations
Removable shelf	Includes one wire shelf for easier storage
One-piece interior liner	Seamless interior for easier cleanup

FS24LMED Specifications:

Overview	
Height of Cabinet	19.63" (50 cm)
Height to Hinge Cap	20.0" (51 cm)
Width	18.5" (47 cm)
Depth	17.63" (45 cm)
Depth with door at 90°	34.5" (88 cm)
Capacity	1.4 cu.ft. (40 L)
Defrost Type	Manual
Door	White
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	0.8
Voltage/Frequency	115 V AC/60 Hz
Weight	35.0 lbs. (16 kg)
Shipping Weight	55.0 lbs. (25 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Freezer	
Door Swing	RHD
Reversible	Factory Reversible
Interior Height	14.38" (37 cm)
Interior Width	13.5" (34 cm)
Interior Depth	13.25" (34 cm)
Shelf Type	Wire
Shelf Qty	1
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.5 oz.
Level Legs	2
Compressor Step Height	8.5" (22 cm)
Compressor Step Width	13.5" (34 cm)
Compressor Step Depth	6.0" (15 cm)

