

# VT65MLPLUS2



33.5" x 23.63" x 23.5" (H x W x D)

24" wide all-freezer for freestanding use, manual defrost with a NIST calibrated thermometer, lock, and -25°C capability

### Highlights:

NIST calibrated thermometer displays the current and high/low temperature to the nearest tenth of a degree

-25° C operation for safe storage of temperature sensitive materials

Ideal 24 footprint offers large capacity in a slim fit

### Product Features:

Slim counter height dimensions	Just 24 wide for an easy fit in tight spots
-25°C capable	Low temperature capability ideal for certain sensitive items
NIST calibrated temperature display	Thermometer provides continuous display of the current and high/low temperature to the nearest tenth of a degree, with a readout switchable from Celsius to Fahrenheit at the touch of a button
Buffered temperature probe	Thermometer probe is encased in a glycol-filled bottle to better simulate the temperature of stored contents instead of freezer air temperature
Factory installed lock	Keyed lock for secure interior
Manual defrost	Efficient performance with reliable temperature stability
Pull-out drawers	Clear baskets for convenient and separated storage
Adjustable thermostat	Manage the temperature with ease and accuracy
Matching refrigerator available	Pair with FF6LPLUS2 for a complete set

## VT65MLPLUS2 Specifications:

Overview	
Height of Cabinet	33.5" (85 cm)
Width	23.63" (60 cm)
Depth	23.5" (60 cm)
Depth with Handle	25.13" (64 cm)
Depth with door at 90°	46.13" (117 cm)
Capacity	3.2 cu.ft. (91 L)
Defrost Type	Manual
Door	White
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	1.3
Shipping Weight	102.0 lbs. (46 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Freezer	
Door Swing	RHD
Reversible	Factory Reversible
Interior Height	24.25" (62 cm)
Interior Width	17.75" (45 cm)
Interior Depth	16.5" (42 cm)
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	2.7 oz.
High Side PSI	235.0
Low Side PSI	70.0
Level Legs	2
Interior Drawers	Yes
Drawers Qty	3
Compressor Step Height	6.5" (17 cm)
Compressor Step Width	17.5" (44 cm)
Compressor Step Depth	5.5" (14 cm)
Temperature Range	-20°C to -30°C

