



Sundström Safety AB
 Västergatan 4, S-341 50 Lagan
 1-887-SUNDSTROM



SR 232 CARTRIDGE (H02-3721)

THIS CARTRIDGE IS APPROVED ONLY IN THE FOLLOWING CONFIGURATIONS																												
RESPIRATOR COMPONENTS																												
TC-	Protection ¹	Cartridge	Alternate Facepiece					Alternate Head Harness				Filter	Accessories												Cautions & Limitations ²			
			SR 200	SR 100 S/M	SR 100 M/L	SR 90-3 S/M	SR 90-3 M/L	U01-1221	T01-1215	U01 - 2001	S-5792		H02-1321	SR 345	SR 64	SR 221	5153-2	R01-0605	SR 322	SR 336	T01-1203	T01-1201	T01-1204	T01-1205		SR 84	ST2-SR	
23C - 1904	OV/SD/CL/HC/HF	X		X	X					X	X			X	X	X	X	X	X								X	ABCHJLMNO
84A - 2662	OV/SD/CL/HC/HF/P100	X		X	X					X	X	X	X	X	X	X	X	X								X	ABCHJLMNOP	
23C-2096	OV/SD/CL/HC/HF	X	X					X	X					X	X	X	X	X	X	X	X	X	X	X	X	X	X	ABCHJLMNO
84A-3381	OV/SD/CL/HC/HF/P100	X	X					X	X					X	X	X	X	X	X	X	X	X	X	X	X	X	X	ABCHJLMNOP
23C-2299	SA/CF/OV/SD/CL/HC/HF	X	X					X	X					X	X						X	X						ABCHJLMNO
84A-4310	SA/CF/OV/SD/CL/HC/HF/P100	X	X					X	X					X	X						X	X						ABCHJLMNOP
23C-2623	OV/SD/CL/HC/HF	X				X	X			X	X			X	X	X	X	X	X	X						X	ABCHJLMNO	
84A-5391	OV/SD/CL/HC/HF/P100	X				X	X			X	X	X	X	X	X	X	X	X	X							X	ABCHJLMNOP	

1. PROTECTION

P100-Particulate Filter (99.97% filter efficiency level) effective against all particulate aerosols.

HF - Hydrogen fluoride CL - Chlorine OV - Organic vapor HC - Hydrogen chloride
 SD - Sulfur dioxide CF - Continuous Flow SA - Supplied-Air

2. CAUTIONS AND LIMITATIONS

- A - Not for use in atmospheres containing less than 19.5 percent oxygen.
- B - Not for use in atmospheres immediately dangerous to life or health.
- C - Do not exceed maximum use concentrations established by regulatory standards.
- H - Follow established cartridge and canister change schedules or observe ESLI to ensure that cartridges and canisters are replaced before breakthrough occurs
- J - Failure to properly use and maintain this product could result in injury or death.
- L - Follow the manufacturer's User's Instructions for changing cartridges, canister and/or filters.
- M - All approved respirators shall be selected, fitted, used, and maintained in accordance with MSHA, OSHA and other applicable regulations.
- N - Never substitute, modify, add, or omit parts. Use only exact replacement parts in the configuration as specified by the manufacturer.
- O - Refer to User's Instructions, and/or maintenance manuals for information on use and maintenance of these respirators.
- P - NIOSH does not evaluate respirators for use as surgical mask.