



ULTRATECH
INTERNATIONAL, INC.

Product Data Sheet

Ultra-Berm Builder

Part# 8640-8645



Build a barrier around machinery or equipment that is permanently mounted or cannot easily be moved

- + Component system provides flexibility to create a semi-permanent, high-visibility custom barrier.
- + Durable, vinyl covering resists oils, coolants and most chemicals.
- + Cut to length and secure to floor with included sealant, then seal seams with the vinyl adhesive.
- + Economical containment for leaks and spills around machinery and equipment - no need to build expensive cement or angle iron curbs.
- + High-visibility yellow color draws attention to barrier for increased safety.
- + Easy removal requires only a flat-bladed shovel.



Part#	Description	Dimensions in. (mm)	Qty	Weight lbs. (kg)
8640	Full kit	50' x 5½" x 2" (15.2 m x 140 mm x 51 mm)	1/box	21.0 (9.5)
8641	Straight Section	15' x 5½" x 2" (4.6 m x 140 mm x 51 mm)	1/box	6.0 (3.0)
8642	Corner	7¼" x 5½" x 2" (184 mm x 140 mm x 51 mm)	2/box	2.0 (1.0)
8643	Connecting Collar	10' x 4" (3m x 102mm)	1/box	1.0 (0.5)
8644	Floor Sealant (10.3 fl. oz. tube)		6/box	8.0 (3.5)
8645	Vinyl Adhesive (8 oz. can)		1/box	1.0 (0.5)

Specifications

Color	Yellow
Dimensions	5.5" W x 50' L x 2" H
Barrier Type	Vinyl berm
Install/Deploy Type	Glued In Place Barrier
Intended Use	For Smooth Surfaces; Walk-On
Max liquid temp exposure	Max Exposure Limit 225°F for up to 30 Minutes
Storage Temp Range	Store Between 0°F and 120°F
Temperature Limit	Works from -22°F to 160°F
# per Pallet	5
Composition	Cover, Seam Mender - 18 oz. Vinyl-Coated Fabric Core - Polyurethane Foam Sealant - Sili-Thane™ 803 Sealant
Shelf life	365 days