


ultra site™

A PLAYCORE® Company



Model # 940P-A8



A PLAYCORE Company

1675 Locust Street
Red Bud, IL 62278
Phone: 618-282-8200
Fax: 618-282-8202

WARRANTY & TERMS

WARRANTY: 5 Year Limited Warranty on Thermoplastic coated elements. Ultra Play guarantees all items for one full year to be free of defects in workmanship or materials when installed and maintained properly. We agree to repair or replace, any items determined to be defective. Items specifically not covered by this warranty include vandalism, man made or natural disasters, lack of maintenance, normal weathering or wear and tear due to public abuse.

Damages or loss in transit is the responsibility of the carrier, whether visible or concealed. It is the responsibility of the recipient to assure that the order is received complete. Before signing the delivery receipt, inspect the shipment immediately and completely. Note any damages or shortages on the bill of lading. Damage reports must be filed within 10 days. Ultra Play is NOT responsible for damages or loss in transit. Title to all goods passes to the customer at the time of shipment. Ultra Play will assist in filing claims if the freight arrangements were made by Ultra Play at your request.

CANCELLATIONS AND RETURNS: Cancellations are only accepted with approval of Ultra Play. No merchandise shall be returned without a Return Goods Authorization number which is issued by customer service. Any authorized merchandise must be carefully packed and received in saleable condition. A restocking charge of up to 25% will be applied to all returned goods when the error is not the fault of Ultra Play. All returns must be shipped freight prepaid.




A PLAYCORE Company


SAFETY WARNINGS & EQUIPMENT INSPECTION

- Owners and installers please note these safety warnings and make use of this checklist on a regular basis.
- Follow installation instructions when erecting equipment.
- Ground surfaces around equipment should be restored as needed. Concrete footings should never be exposed. Surface depth should comply with ASTM and CPSC specifications.
- Check for and repair damage caused by wear or vandalism, a major factor in injury causing situations.
- All protruding bolts should be covered or cut off and finished smooth. Sharp edges on pipes should be capped or removed. Check for bent, broken, or severely worn pipe, and replace.
- All equipment should be free of rust and repainted whenever necessary to deter rusting.
- We provide our customers with layout sheets and installation instructions. Please keep on file the specifications sheet that contains the listing of every part used.
- Never add components not intended for use with this product.
- Regular maintenance is necessary in this and all park and recreational equipment to insure the safety of the user.
- Note: Proper maintenance of equipment requires regular tightening of all bolts, nuts, and setscrews.
- Note: Regular checking of all parts, castings, etc. should be made. If a part is broken or worn, it should be replaced immediately.
- Check to be sure all fittings are tight and that bars and pipes do not move.
- Replace all worn S-hooks. S-hooks must be completely closed. Failure to close S-hooks can result in serious injury to the user. NEVER reuse S-hooks.
- Test for free movement of swing hanger and other moving attached parts.
- Check for worn chains and replace them.
- A soft resilient surface should be placed under all swings extending at least twice the height of the top rail both front and back.


HARDWARE




5/16" x 1-1/4"
Carriage Bolt




3/8" x 3"
Carriage Bolt



3/8" Washer



5/16" Washer




3/8" Hex Nut




5/16" Hex Nut


TOOLS REQUIRED




1/2" & 9/16"
Wrench



1/2" & 9/16"
Socket Wrench



Tape Measure



Level

ULTRA SITE PRODUCT SPECIFICATIONS

940P-A8 PORTABLE BENCH WITH BACK

Seats & Back: 2' x 10' seat planks are anodized aluminum alloy 6063-T6 extrusions. Planks shall have a thickness of not less than .078 and a fluted non-skid surface. 2" x 10" anodized aluminum extrusion.

Frame: 2-3/8" O.D. x 12 gauge pre-galvanized structural steel tubing. Seat/back support is bent over a mandrel through the bend radius producing a wrinkle free bend. Tube ends are pre-galvanized steel capped. Cross braces are 1 5/16" O.D. x 14 gauge pre-galvanized structural steel tubing. All electrically MIG welded.


Frame Coating: Electrostatic powder coated application oven cured or hot dipped galvanized.

Hardware: All zinc hardware fasteners.

Dimensions: 8' bench portable with back. Seats and back are 9-3/4" wide x 96-1/4" long. Seat height is 18", seat back height is 34-1/4". Total depth of seat with back is 21-1/2".

COMPONENTS

Attach the Aluminum Planks and the 73-5/8" Brace to the 942 Frames as shown using specified hardware.



Clips hang on the inside of the Planks as shown.

ITEM NO.	PartNo	DESCRIPTION	QTY
1	P-W940P	940 Portable Wood Leg	2
2	AA96-C	8' Alum Plank w/ endcap	2
3	22-01-0062	Alum. Planking Clip	8
4	33-06-0010	5/16" x 3-1/4" Carriage Bolt (Zinc)	8
5	33-06-0008	3/8" x 3" Carriage Bolt (Zinc)	2
6	33-02-0001	5/16" Zinc Plated Washer	8
7	33-02-0002	3/8" Zinc Plated Washer	2
8	33-01-0001	5/16" Hex Nut (Zinc)	8
9	33-01-0002	3/8" Hex Nut (Zinc)	2
10	03-04-0100	73 5/8" Brace	1

OVERALL DIMENSIONS

