



No.:

Date: 28-DEC-2012

Customer :

TECHNICAL PROPOSAL

Single-phase induction motor - Squirrel cage rotor

Product line : Pool & Spa Motors : C-Face - Start Capacitor - Low Service Factor

Catalog Number : PCJ107

List Price : \$236

Notes:

Performed by:

Checked:



No.:

Date: 28-DEC-2012

## DATA SHEET

### Single-phase induction motor - Squirrel cage rotor

Customer :  
 Product line : Pool & Spa Motors : C-Face - Start Capacitor - Low Service Factor

Frame : K56J  
 Output : 0.75 HP  
 Frequency : 60 Hz  
 Poles : 2  
 Full load speed : 3465  
 Slip : 3.75 %  
 Voltage : 115/230 V  
 Rated current : 10.2/5.10 A  
 Locked rotor current : 54.1/27.0 A  
 Locked rotor current (I<sub>L</sub>/I<sub>n</sub>) : 5.3  
 No-load current : 7.70/3.85 A  
 Full load torque : 1.12 lb.ft  
 Locked rotor torque : 140 %  
 Breakdown torque : 260 %  
 Design : ---  
 Insulation class : B  
 Temperature rise : 80 K  
 Locked rotor time : 6 s (hot)  
 Service factor : 1.30  
 Duty cycle : S1  
 Ambient temperature : -20°C - +50°C  
 Altitude : 1000  
 Degree of Protection : IP21  
 Approximate weight : 23 lb  
 Moment of inertia : 0.02326 sq.ft.lb  
 Noise level : ---

	D.E.	N.D.E.	Load	Power factor	Efficiency (%)
Bearings	6203 2RS	6203 ZZ	100%	0.72	66.2
Regreasing interval	---	---	75%	0.63	62.5
Grease amount	---	---	50%	0.53	55.0

Notes:

Performed by


Checked



No.:

Date: 28-DEC-2012

PERFORMANCE CURVES RELATED TO RATED OUTPUT  
Single-phase induction motor - Squirrel cage rotor




Customer :  
Product line : Pool & Spa Motors : C-Face - Start Capacitor - Low Service Factor

Frame	: K56J	Locked rotor current (I <sub>l</sub> /I <sub>n</sub> )	: 5.3
Output	: 0.75 HP	Duty cycle	: S1
Frequency	: 60 Hz	Service factor	: 1.30
Full load speed	: 3465	Design	: ---
Voltage	: 115/230 V	Locked rotor torque	: 140 %
Rated current	: 10.2/5.10 A	Breakdown torque	: 260 %
Insulation class	: B		

Notes:

Performed by

Checked



Notes:

Performed by:

Checked:

Customer:

Pool & Spa Motors : C-Face - Start Capacitor - Low Service Factor

P	C	AA	Flange	AJ
5.748	13.898	NPT 1/2"	FC-149	5.874
AK	BD	BF	BB	BC
4.500	5.748	UNC 3/8"x16	0.157	---
AH				
2.563				

Single-phase induction motor  
Frame K56J - IP21

28-DEC-2012

