



ALLURE 36" SHOWER DOOR
(without stationary panel)

The ALLURE™ will give your bathroom a fresh perspective with clean lines and a flexible design. The versatile ALLURE is available in sizes to fit a wide range of openings from 30 to 67 inches wide. Smart wall profiles and unique pivot hardware provide up to 7 inches of installation adjustments. Premium 3/8" thick tempered glass delivers the look and feel of custom glass.




ALLURE SHOWER DOOR WITH 24" SIDE PANEL
AND OPTIONAL SHOWER BASE

ALLURE

- 3/8" (10mm) tempered clear glass
- Reversible for right or left door opening
- Unique adjustable pivot door hardware
- Up to 7" width total adjustment on all doors (1" in wall profile for width or out-of-plumb and 6" in pivot hardware for width)
- Additional stationary side glass panel with 2 shelves included for doors wider than 43"
- Anodized aluminum profiles
- Visible fixtures in chrome finish (profiles and pivot hardware)
- Optional single threshold fiberglass reinforced Acrylic/ABS base
- Optional Acrylic/ABS back wall kit

ALLURE SHOWER DOOR


**ADJUSTABLE
HARDWARE**



Pivot Mechanism up to 6" for width adjustment




Wall profile up to 1/2" for out of plumb adjustment



Stationary Panel Wall Profile
Up to 1" for width and out-of-plumb adjustment



Door Handle



Glass Shelves




Optional Shower Base



no panel configuration

Model Number
SHDR-4230728-01
SHDR-4236728-01

Width Range
30" - 37"
36" - 43"



12" panel configuration

Model Number
SHDR-4242728-01
SHDR-4248728-01

Width Range
42" - 49"
48" - 55"



24" panel configuration

Model Number
SHDR-4254728-01
SHDR-4260728-01

Width Range
54" - 61"
60" - 67"

