


DYMO

LabelManager[®]

PNP

Plug and Play Label Maker for PC or Mac[®]



Just plug, type and print – it's that easy!

Finally, printing a label is fast and easy! With the LabelManager PnP label maker there's no software to install – just plug it into your PC¹ or Mac^{®2}, and you're ready to create great-looking labels as fast as you can type! Plus you can customize your labels using the fonts and graphics on your computer.

LabelManager[®] PnP Features

- 1 Connect via USB to your PC¹ or Mac^{®2}
- 2 Easy to take with you and connect to any laptop
- 3 No software to install
- 4 Built-in software pops up on your computer screen, ready to use
- 5 Also includes free download of DYMO[™] Label Software v8 – print logos, batch labels from database files, and much more
- 6 Customize your label with any fonts or graphics on your computer
- 7 No power adapter or AA batteries needed
- 8 Uses 1/4", 3/8" and 1/2" DYMO D1 labels



Plug



Type and Print



Easy!



DYMO[®] Label[™] Software

DYMO Label[™] v.8 Works with any fonts or graphics on your computer – customize with your company logo and much more!

Multi-application Print labels from within Microsoft[®] Word, Excel[®] or Outlook[®], Mac[®] Address Book, QuickBooks[®] and other programs

PC or Mac[®] Works with Windows[®] XP, Windows Vista[®], Windows[®] 7 or Mac OS[®] X 10.4 or later – Intel[®] only



¹ Windows Vista[™], Windows[®] 7, Windows[®] XP ² Mac OS[®] v10.5.8 or later



D1 Labels

Standard, Permanent or Flexible...
no labels are more durable.



Standard labels* for hundreds of tasks around the office or home office, such as filing, storage, asset management, and reminders. Available in continuous label cassettes, you can create sharp, easy-to-read labels of just about any length.



Permanent labels look the same as standard labels but offer a powerful, permanent adhesive for when you want a label to stay put indefinitely.



Flexible labels are for curved and/or heavily textured surfaces and flag-marking cables. Its permanent adhesive means it will stay put.



Easy Peel



UV Resistant



Water Resistant



*Temperature: -40° F to 194° F

LabelManager® PnP Specifications

Item #1768960 List Price: \$89.99

LabelManager® PnP Pack Content

- Electronic label maker
- D1 starter label cassette, black on white, 1/2" x 11.5'
- Lithium-ion rechargeable battery
- USB cable
- Changing adapter
- Quick Start Guide
- 1-Year Limited Warranty Card

LMPnP Pack Unit

Length	6.8"
Width	3.2"
Height	8.8"
Weight (lbs)	1.6

Shipper

Length	19.9"
Width	9.3"
Height	8.0"
Weight (lbs)	9.6

D1 labels for the LabelManager® PnP

Standard (available in 1/4", 3/8" and 1/2" x 23') List Price: \$19.67

	BLACK•WHITE	RED•WHITE	BLACK•YELLOW	BLACK•RED	BLACK•CLEAR	RED•CLEAR
1/4"	43613	-	-	-	43610	-
3/8"	41913	40915	-	-	40910	-
1/2"	45013	45015	45018	45017	45010	45012

	BLUE•WHITE	WHITE•BLACK	BLACK•BLUE	BLACK•GREEN	WHITE•CLEAR	BLUE•CLEAR
1/4"	-	-	-	-	-	-
3/8"	40914	-	-	-	-	-
1/2"	45014	45021	45016	45019	45020	45011

Flexible (available in 1/2" x 11.5')
List Price: \$18.80 (1/2")

	BLACK•WHITE
1/2"	16953

Permanent (available in 1/2" x 18')
List Price: \$18.80 (1/2")

	BLACK•WHITE
1/2"	16955

