



fitted with

- work equipment**
- connected load**
- power consumption**
- glare-free**
- system of protection**
- class of protection**
- usage**
- luminaire body**
- material
- color
- lamp cover**
- tubular sections**
- material
- arm
- color
- balance of articulation joints**
- weight (net)**
- mains lead**

- 36 x LED
- color temperature 3800-4300K
- color rendering index (CRI) = 80
- electronic transformer
- 100-240V, 50/60Hz
- approx. 47W
- clear prismatic lens
- IP20
- II
- multi-function switch

- anodized aluminum
- silver
- clear acrylic

- aluminum
- dual spring loaded
- silver
- spring
- approx. 5lb (2.3kg)
- approx. 11ft (3.3m) with plug

fastening

table clamp or wall mount optional



illuminance

measuring conditions: d=50cm

E_{min}: 228 lx
 E_m: 1425 lx
 E_{max}: 3596 lx

