



fitted with


- work equipment**
- connected load**
- power consumption**
- system of protection**
- class of protection**
- technology**
- usage**
- luminaire body**
- material
- surface
- color
- lamp cover**
- tubular sections**
- material
- color
- balance of articulation joints**
- weight (net)**
- mains lead**
- fastening**
- lens; dimensions**
- lens; diopters**
- add-on lens; dimensions**
- lens; diopters
- special features

- 48 x LED
- color temperature: 3700-4000K
- color rendering index (CRI) = 90
- electronic plug-in transformer
- 100-240V, 50/60Hz
- approx. 14W
- IP20
- II
- multi stage switchable; continuously dimmable
- multi-function switch

- plastic
- untreated
- black
- Acrylic satine

- anodized tubular aluminum
- silver
- spring
- approx. 2.7kg (6lbs)
- approx. 3.4m (11ft); US and Euro plugs incl.
- Table Clamp
- Ø 160mm (6.3in)
- 3.5
- Ø 31.5mm (1.24in)
- 8
- segment switched LED

illuminance



measuring conditions: d=15cm

E_{min}: 1377 lx
E_m: 4002 lx
E_{max}: 6141 lx

