



fitted with

- work equipment**
- connected load**
- power consumption**
- system of protection**
- class of protection**
- technology**
- usage**
- luminaire body**
- material
- surface
- colour
- lamp cover**
- weight (net)**
- mains supply**

- design**
- fastening**
- dimension**
- special features**

- 48 x Light-emitting diode
- light colour neutral white, 4600-5400 K, Color Rendering Index (CRI)=85
- power supply unit
- 100/120/220-240 V; 50/60 Hz
- approx. 27 W
- IP 67
- I
- switchable
- without switch
- aluminium
- anodised
- aluminium coloured anodised
- screen, clear
- approx. 2.3 kg
- built-in plug
- Serie 814
- mounted version
- L-angle, clamp
- A=650 mm
- Power equipment




Serie 814

illuminance

measuring conditions: d=100cm

Em: 657 lx
Emax: 856 lx
Emin: 408 lx



luminous intensity

