

PaperSAFE®

OIL free Shredders



The most convenient way to destroy confidential information

PaperSAFE® are oil-free shredders by Dahle that offer best-in-class features and noise reduction to support a productive work environment.

Oil-Free Shredding

Wondering when your shredder was last oiled is no longer a concern. Through clever engineering, these machines maintain peak performance without oil. PaperSAFE® shredders are not only convenient to use and economical to maintain, but also easier on the environment.

Whisper Quiet

PaperSAFE® features Whisper Quiet operation that produces the lowest decibel levels in their class. They're perfect for shredding in a quiet office and not disturbing others nearby or on the phone.

Jam Protection

With built-in jam protection, these shredders prevent frustrating paper jams. If sheet capacity is exceeded, the motor automatically stops and reverses to push the paper back out.

Convenience

Most models feature automatic on/off, bin-full auto off, and energy saving standby mode to make these shredders convenient to use, easy to maintain, and environmentally friendly.

Oil Free / Hassle Free	Whisper Quiet Operation
Built-In Jam Protection	Shreds CDs, CCs, Staples & Clips



22022

Sheet Capacity: 7 / 9
Waste Volume: 4 gal.
Oil-Free Shredder



22092

Sheet Capacity: 10 / 12
Waste Volume: 4 gal.
Oil-Free Shredder



22312

Sheet Capacity: 15 / 17
Waste Volume: 7 gal.
Oil-Free Shredder



22318

Sheet Capacity: 16 / 18
Waste Volume: 9 gal.
Oil-Free Shredder



22080

Sheet Capacity: 6 / 8
Waste Volume: 9 gal.
80 Sheet Auto Tray

Specifications

Model	Feed Width	Capacity #20 / #16	Security Level	Shred Size		Waste Volume	Speed	Decibel Level	Special Features					Warranty		Dimensions length x width x height	Weight
				paper	media				Oil-Free	Jam Protection	Bin-Full Auto-Off	CDs DVDs	Staples / Clips	Shredder	Cylinders		
22022	8.75"	7 / 9	P-4	3/16" x 1 3/16"	-na-	4 gal	10 f/m	59 dB	●	●				1 year	5 years	7" x 12.5" x 15.5"	8 lbs
22092	8.75"	10 / 12	P-4	3/16" x 1 3/8"	1"	4 gal	14 f/m	62 dB	●	●	●	●		1 year	5 years	7.75" x 12.25" x 16.5"	14 lbs
22312	8.75"	15 / 17	P-4	3/16" x 1 7/16"	1.5"	7 gal	9 f/m	53 dB	●	●	●	●	●	1 year	5 years	11" x 14.25" x 21"	24 lbs
22318	8.75"	16 / 18	P-4	3/16" x 1 1/16"	3/16" x 1 1/16"	9 gal	11 f/m	52 dB	●	●	●	●	●	1 year	5 years	13" x 15.5" x 25.5"	32 lbs
22080	8.75"	6 / 8	P-4	1/8" x 3/8"	1"	9 gal	11 f/m	52 dB	●	●	●	●	●	1 year	5 years	10.75" x 15" x 21"	26 lbs

Performance data established using #20 / #16 bond 8 1/2" x 11" paper. Different paper qualities may yield different results.

Dahle North America, Inc.
49 Vose Farm Road
Peterborough, NH 03458
(800) 995.1379 / www.dahle.com

