


7FLEX[®] DUAL

For PC and iMac[®]

Now you can mount two of our best-selling 7Flex[®] LCD Arms from one point on your desk. Effortlessly reposition each monitor with just one hand. You will free up desk space, even as you work in greater ergonomic comfort. The dual mount can be clamped to desk edge or grommet, or bolted through the desk.

PRODUCT FEATURES:

- Product Includes: FLEXmount™ with six mounting options (see page 2) & VESA adapter plate (75X75 and 100X100)
- Compatible with all VESA displays, including the 2012-present 21.5" iMac[®]
- Offers 16" of dynamic one-touch height adjustment
- Full extension range of 24"
- Slim profile design folds up flat to occupy just 3.5" of space
- Monitor Weight Capacity: 5lbs - 17lbs per arm
- Tilt: UP 200° / Pan: 180°
- Rotation: 360° at three joints
- Integrated cable management system hides cables and keeps your work surface free of clutter
- Available Colors: Black
- Part Code: 7Flex-Dual-ETUS-104




Quickly adjust monitor position as your needs change



Includes integrated cable management




Clamps to desk edge or through




Choose Your Own Mount!

7Flex comes equipped with SIX mounting options, giving you the ability to adapt to any workspace setup you may have.

7 FLEX[®] DUAL



SIDE VIEW
Vertical Range









TOP VIEW
Horizontal Range

CAPABILITIES

- Vertical range +/- 8.0" (20.3 cm) from horizontal
- Horizontal range, per arm 24.0" (61.0 cm)
- Rotation 360 degrees at three joints
- Monitor tilt 200 degrees
- Monitor pivot Landscape to portrait
- Monitor compatibility VESA[®] 75mm and 100mm
- Cable management Cables are clipped beneath arm
- Mounting options Desk Edge, Grommet, Thru-Desk, Side Bolt
- Monitor weight, model number 5 - 17 lbs (2.3 - 7.7 kg), 7Flex-Dual-104i

FLEXMOUNT™ CONFIGURATIONS

		
Desk Clamp	Thru-Desk	Wall
		
Grommet	Side Bolt	Reverse Wall