



A R I A

Low Profile Glassboards

THE MOST SECURE
GLASSBOARD





The Most Secure Glassboard On The Market

Most Secure – heavy-duty hanging system gives confidence the board will never bow, strain, or move from the wall, creating a safe user experience.

Low Profile – 1/4" tempered glass floats only 1/2" from the wall surface, giving the illusion of floating glass.

Integrated – magnetic markers adhere under the glassboard allowing for a clutter-free writing surface.

Limitless – design your space by choosing to hang Aria vertically, horizontally, singular, or as a glass wall.

Quality – non-porous glass surface works with standard dry-erase markers and will not ghost or stain – guaranteed.

Sustainable – 100% recyclable; composed of recycled glass and sand.



A Striking Composition Of Function Meeting Elegance.

Aria low profile glassboards achieve the look of weightless, floating glass, creating a feeling of opulence from every angle. No visible hardware or standoffs allow the beauty of the glass to complement any décor. Our team of engineers developed a heavy-duty hanging system that promotes security and confidence that your board will never bow, strain, or move from the wall. With multiple orientation options, Aria can be used as a single board for personal offices and conference rooms, or designed as a glass wall, optimizing brainstorming and collaboration spaces.

- 1/4" tempered low profile glassboard floats only 1/2" from the wall surface
- Installed with heavy-duty aluminum cleating and a steel support bar that work together to safely secure the glassboard to the wall
- One-of-a-kind hanging process allows Aria to be mounted to any surface, including uneven surfaces like brick or concrete
- Integrated underneath marker storage allows for an uncluttered writing surface
- Concealed hardware creates a clean, frameless, and superior dry-erase surface
- Available in square edges, magnetic, or non-magnetic surface
- Choose from eight standard colors; custom colors also available
- Unlimited design options—hang vertically or horizontally, as a single board, or build a glass wall by joining multiple boards side by side
- Backed by Ghent's 50-year warranty




GY

Gray



YW

Yellow



BE

Blue



WH

White




GN

Green




BG

Beige




PH

Peach




BK

Black*



CUSTOM
COLORS
AVAILABLE



Square Corners



Integrated Marker Storage

Depending on lighting, angles, orientation, and wall color, glassboard appearance can vary.

*Black glassboards require wet-erase markers, not dry-erase markers. Wet-erase markers are included with Black glassboard purchases.



3 Black 4' x 8' Aria low-profile glassboards shown as a glass wall.

Item No. Description

Non-Magnetic - Horizontal	
ARIASN23XX	2'H x 3'W Low Profile 1/4" Glassboard - Horizontal
ARIASN34XX	3'H x 4'W Low Profile 1/4" Glassboard - Horizontal
ARIASN44XX	4'H x 4'W Low Profile 1/4" Glassboard - Horizontal
ARIASN45XX	4'H x 5'W Low Profile 1/4" Glassboard - Horizontal
ARIASN46XX	4'H x 6'W Low Profile 1/4" Glassboard - Horizontal
ARIASN48XX	4'H x 8'W Low Profile 1/4" Glassboard - Horizontal

Non-Magnetic - Vertical

ARIASN32XX	3'H x 2'W Low Profile 1/4" Glassboard - Vertical
ARIASN43XX	4'H x 3'W Low Profile 1/4" Glassboard - Vertical
ARIASN44XX	4'H x 4'W Low Profile 1/4" Glassboard - Vertical
ARIASN54XX	5'H x 4'W Low Profile 1/4" Glassboard - Vertical
ARIASN64XX	6'H x 4'W Low Profile 1/4" Glassboard - Vertical
ARIASN84XX	8'H x 4'W Low Profile 1/4" Glassboard - Vertical

i.e. ARIASM23BK

ARIA | S – Square Corners | M – Magnetic | 23 – Board Size (2' H x 3' W) | BK – Black

i.e. ARIASN32PH

ARIA | S – Square Corners | N – Non-Magnetic | 34 – Board Size (3' H x 2' W) | PH – Peach

Each Non-Magnetic Aria glassboard includes 4 markers and 1 eraser.

Each Magnetic Aria glassboard includes 4 markers, 1 eraser and 4 rare earth magnets.

Item No. Description

Magnetic - Horizontal	
ARIASM23XX	2'H x 3'W Magnetic Low Profile 1/4" Glassboard - Horizontal
ARIASM34XX	3'H x 4'W Magnetic Low Profile 1/4" Glassboard - Horizontal
ARIASM44XX	4'H x 4'W Magnetic Low Profile 1/4" Glassboard - Horizontal
ARIASM45XX	4'H x 5'W Magnetic Low Profile 1/4" Glassboard - Horizontal
ARIASM46XX	4'H x 6'W Magnetic Low Profile 1/4" Glassboard - Horizontal
ARIASM48XX	4'H x 8'W Magnetic Low Profile 1/4" Glassboard - Horizontal

Magnetic - Vertical

ARIASM32XX	3'H x 2'W Magnetic Low Profile 1/4" Glassboard - Vertical
ARIASM43XX	4'H x 3'W Magnetic Low Profile 1/4" Glassboard - Vertical
ARIASM44XX	4'H x 4'W Magnetic Low Profile 1/4" Glassboard - Vertical
ARIASM54XX	5'H x 4'W Magnetic Low Profile 1/4" Glassboard - Vertical
ARIASM64XX	6'H x 4'W Magnetic Low Profile 1/4" Glassboard - Vertical
ARIASM84XX	8'H x 4'W Magnetic Low Profile 1/4" Glassboard - Vertical

