

3315B SERIES CAFE CHAIRS

Model: 3315B
In Stock with:
Natural, Mahogany and
Walnut Seat and Back



Mahogany Walnut Natural



UPHOLSTERY OPTIONS:

- 1 - KFI House Upholsteries and Vinyl's
- 2 - Grade-In Options from:
Mayer
Momentum
Spradling
Guilford of Maine
- 3 - COM (Customer's Own Material)

(Lead-Time on non-stock products-
 4 to 5 weeks)

1 - SEAT:

A - 2" Upholstered Seat- See Upholstery Options

B - Wood seat & back colors available:

(ST16) Natural, (ST02) Honey, (ST03), Dark Cherry, (ST19) LT. Mahogany,
 (ST08) Walnut, Green (ST15), (ST06) Black, (ST05) Sage



Weight Tested
 to hold 400 lbs

2 - POWDERCOAT FRAME FINISH:

Shiny Black (BK), Sandtex Black (SB), Silver Vein (SV), Gold Vein (GV), Copper Vein (CV),
 Silver (SL) and Nickel (NK), Chrome (CH)

| Specification | Description |
|----------------------------|--|
| A - Type Frame | 1 1/4" Square Steel Tubing - 18 gauge Steel made from 59% post-consumer scrap, 33% post industrial |
| B - Foam | 100% Virgin Polyurethane Hi-Density California TB-117 - Standard Boston Fire Code - Optional |
| C - Glides | Four Clear Polyurethane- Self Leveling |
| D - Dimensions, Overall | |
| 1 - Height | 32" |
| 2 - Depth | 19" |
| 3 - Width | 17.25" |
| 4 - Seat Size | 17" x 16" |
| 5 - Seat Height from floor | 18" |
| 6 - Weight Capacity | 400 lbs |
| 7 - Ship Weight | 18 lbs |



Small Business
 HUBZone

