

# BR1310 SPEC SHEET-Upholstered Back



## UPHOLSTERY OPTIONS:

1 - KFI House Upholsteries and Vinyl's

2 - Grade-In Options from:  
**Mayer**  
**Momentum**  
**Spradling**  
**Guilford of Maine**

3 - COM (Customer's Own Material)



Small Business  
HUBZone

**Made in USA**



Chair is 95% recyclable after its useful life.\*

A. SEAT: 1.5" Upholstered

B. BACK: Contoured, Upholstered

B. FRAME FINISH :

1 - Sandtex Black (SB) or Silver (SL)

2 - Chrome (CH) - (All models - 50 min. on chairs / 100 min. on barstool)

| Specification                  | Description  |
|--------------------------------|--|
| A - Type Frame                 | 7/8" Round Tubing Legs, 16 Gauge   |
| B - Number of Welds            | 32 Point Welds (arm and armless)   |
| C - Stretcher                  | 5/8" Square Tubing - 18 gauge  |
| D - Foam                       | 100% Virgin Polyurethane Hi-Density<br>California TB-117 - Standard<br>Boston Fire Code - Optional |
| E - Glides                     | Four Black Polyethylene  |
| F - Weight Capacity            | Standard ANSI-BIFMA test- 250lbs   |
| <b>G - Dimensions, Overall</b> |  |
| 1 - Height                     | 45"  |
| 2 - Depth                      | 22"  |
| 3 - Width                      | 19"  |
| 4 - Seat Size                  | 1.5" x 17.5"W" x 17.5"   |
| 5 - Seat Height from floor     | 29"  |
| 6 - Back Dimensions            | 18"W x 12"H  |
| H - Stool Weight               | 18 lbs   |

