



No.:

Date: 28-DEC-2012

Customer :

TECHNICAL PROPOSAL

Single-phase induction motor - Squirrel cage rotor

Product line : Jet Pump - NEMA 56 : Single-Phase - Keyed - TEFC (IP55)

Catalog Number : .7536ES1BJP56C

List Price : \$320

Notes:

Performed by:

Checked:



No.:

Date: 28-DEC-2012

DATA SHEET

Single-phase induction motor - Squirrel cage rotor

Customer :
Product line : Jet Pump - NEMA 56 : Single-Phase - Keyed - TEFC (IP55)

Frame : B56
Output : 0.75 HP
Frequency : 60 Hz
Poles : 2
Full load speed : 3490
Slip : 3.06 %
Voltage : 115/208-230 V
Rated current : 10.4/5.00-5.20 A
Locked rotor current : 65.5/32.8 A
Locked rotor current (I_L/I_n) : 6.3
No-load current : 7.60/3.80 A
Full load torque : 1.11 lb.ft
Locked rotor torque : 300 %
Breakdown torque : 290 %
Design : ---
Insulation class : B
Temperature rise : 80 K
Locked rotor time : 6 s (hot)
Service factor : 1.15 (1.00 at 208V)
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000
Degree of Protection : IP55
Approximate weight : 29 lb
Moment of inertia : 0.03963 sq.ft.lb
Noise level : ---

	D.E.	N.D.E.	Load	Power factor	Efficiency (%)
Bearings	6203 2RS	6202 2RS	100%	0.72	64.0
Regreasing interval	---	---	75%	0.64	60.0
Grease amount	---	---	50%	0.54	52.0

Notes:

Performed by


Checked



No.:

Date: 28-DEC-2012

PERFORMANCE CURVES RELATED TO RATED OUTPUT Single-phase induction motor - Squirrel cage rotor




Customer :
Product line : Jet Pump - NEMA 56 : Single-Phase - Keyed - TEFC (IP55)

Frame : B56	Locked rotor current (I _l /I _n) : 6.3
Output : 0.75 HP	Duty cycle : S1
Frequency : 60 Hz	Service factor : 1.15 (1.00 at 208V)
Full load speed : 3490	Design : ---
Voltage : 115/208-230 V	Locked rotor torque : 300 %
Rated current : 10.4/5.00-5.20 A	Breakdown torque : 290 %
Insulation class : B	

Notes:

Performed by

Checked



Notes:

Performed by:

Checked:

Customer:

Jet Pump - NEMA 56 : Single-Phase - Keyed - TEFC (IP55)

2E	H	BA	A	P
4.874	0.342	2.750	6.535	7.323
D	J	O	AB	AA
3.500	1.220	7.165	5.433	NPT 1/2"
Flange	AJ	AK	BD	BF
FC-149	5.874	4.500	6.535	UNC 3/8"x16-2B
BB	BC	AH		
0.157	---			

Single-phase induction motor
Frame B56 - IP55

28-DEC-2012

