


# portable heater

**HFC  
1500  
SERIES**

**LOW PROFILE / MARINE**




**FEATURES:**

- Open-Coil Element
  - C-Frame Moto
  - Squirrel Cage Blower
  - Built-In Thermostat
  - Quiet Running
- Metal case and grille
  - Powder-coated finish
  - Manual reset limit
  - Secondary unit protection: one shot fuse
  - Two heat settings: 750/1500 Watts
  - Low temperature thermostat setting
  - Fan-only setting
  - Automatic thermostat
  - 8 foot, 3-conductor grounded power cord
  - Standard color: two-tone light gray / dark gray grille



**This small, quiet desktop portable** is intended for use in the RV and marine environment for quick heating and freeze protection. A 750 Watt setting, along with a low temperature thermostat setting, allows this portable to be used for freeze protection. The 1500 Watt setting allows it to be a comfort heater. An 8 ft. grounded cord makes it convenient to reach distant power outlets.



- ① = OFF
- ☪ = FAN ONLY
- ① = 750 Watts
- ② = 1500 Watts

**SELECTION:**

WATTAGES		MODEL	DESCRIPTION	UPC #25526 PART #	VOLTAGE	AMPS		LENGTH OF CORD	DIMENSIONS	WT. (lbs.)	CASE QTY.
LO	HI					LO	HI				
750	1500	HFC-1500	Low Profile Marine	01200	120V	6.25	12.5	8 ft.	10" L x 10 1/4" W x 4 3/4" H	6	6 (38 lbs.)



Small compact size



Point-of-purchase packaging

Perfect for marine applications!

