



PORTABLE FIRE EXTINGUISHERS



ABC MULTI-PURPOSE DRY CHEMICAL

REGULARLY FURNISHED: Red glossy polyester coated steel cylinder with pressure gauge, wall mounting bracket and hose or nozzle as indicated. Contents stored under pressure at approximately 195 PSI.

✓ Model No.	Size lbs. / kg	U/L Rating	FM Appv'l	Height	Dia.	Range of Stream	Type Discharge
3002	2-1/2 / 1.1	1A:10B:C	Yes	14-3/4"	3"	9'-15'	Nozzle
3005	5 / 2.3	2A:10B:C	Yes	15-1/4"	4-1/4"	12'-18'	Hose
3005-3	5 / 2.3	3A:40B:C	No	15-1/4"	4-1/4"	12'-18'	Hose
3006	6 / 2.7	3A:40B:C	Yes	16"	5"	15'-21'	Hose
3010	10 / 4.5	4A:80B:C	Yes	20"	5"	15'-21'	Hose
3020	20 / 9	20A:120B:C	Yes	23-1/4"	7"	15'-21'	Hose



ABC MULTI-PURPOSE CARTRIDGE OPERATED DRY CHEMICAL

REGULARLY FURNISHED: Red glossy polyester coated steel cylinder with hose, squeeze grip control nozzle and wall mounting bracket. Carbon dioxide gas contained in outside cartridge at approximately 850 PSI (70°F) provides cylinder pressurization and agent discharge upon activation.

✓ Model No.	Size lbs. / kg	U/L Rating	FM Appv'l	Height	Dia.	Overall Width	Range of Stream	Type Discharge
3052	10 / 4.5	4A:60B:C	No	18-1/2"	5-1/4"	9"	18'-22'	Hose
3054	20 / 9	20A:80B:C	No	21-1/2"	6-3/4"	10-3/4"	18'-22'	Hose
3056	25 / 11.3	20A:120B:C	No	26-1/4"	6-3/4"	10-3/4"	18'-22'	Hose



PRESSURIZED WATER/F.F.F.P. FOAM

REGULARLY FURNISHED: Stainless steel shell with pressure gauge and wall mounting bracket. Shipped empty, to be charged at destination by authorized personnel.

✓ Model No.	Size Gal. / Lt	U/L Rating	FM Appv'l	Height	Dia.	Range of Stream	Type Discharge
3202 (Water)	2-1/2 / 9.4	2A	Yes	24-1/2"	7"	45'-55'	Hose
3252 (Foam)	2-1/2 / 9.4	3A:20B	No	24-1/2"	7"	10'-15'	Hose & Nozzle



BC DRY CHEMICAL

REGULARLY FURNISHED: Red glossy polyester coated steel cylinder with pressure gauge, wall mounting bracket and hose or nozzle as indicated. Contents stored under pressure at approximately 195 PSI.

✓ Model No.	Size lbs. / kg	U/L Rating	FM Appv'l	Height	Dia.	Range of Stream	Type Discharge
3302	2-1/2 / 1.1	10B:C	Yes	14-3/4"	3"	9'-15'	Nozzle
3305	5 / 2.3	10B:C	Yes	15-1/4"	4-1/4"	12'-18'	Nozzle
3305-3	5-1/2 / 2.5	40B:C	No	15-1/4"	4-1/4"	12'-18'	Hose
3306	6 / 2.7	40B:C	Yes	16-3/4"	5"	15'-21'	Hose
3310	10 / 4.5	60B:C	Yes	20"	5"	15'-21'	Hose
3320	20 / 9	120B:C	Yes	23-1/4"	7"	15'-21'	Hose

MEMBERS:



REV. 11/17/04

MODEL NUMBER

3002 - 3320