

7000 SERIES FIRE EXTINGUISHER CABINETS

REGULARLY FURNISHED:

BOX- Cold rolled steel with an electrostatically applied, thermally-fused polyester coating with recoatable white finish, and a continuous hinge.

DOOR AND FRAME


7007-7029 Series: Steel - Cold rolled steel with recoatable white polyester finish.

7030-7049 Series: Aluminum - Satin finish, clear polyester coated.


7050-7069 Series: Stainless Steel - #304 Stainless Steel with #4 finish.

7070-7089 Series: Brass - Polished finish, clear polyester coated.


Wall mounting and size of cabinet as selected by model number.




RECESSED



TRIMLESS



SEMI-RECESSED



SURFACE

| Qty | Model No. | | | | Wall Mounting | Inside Box Dimensions | | | Overall Frame | | Minimum Wall Opening Required | | | Trim | ADA | For Use With These Extinguishers |
|-----|-----------|----------|-----------------|-------|---------------|--------------------------------|--------------------------------|-------------------------------|--------------------------------|--------------------------------|-------------------------------|----|-------------------------------|------|-----|--|
| | Steel | Aluminum | Stainless Steel | Brass | | K | L | M | N | O | W | H | D | | | |
| | 7007 | 7037 | 7057 | 7077 | Recessed | 9 | 18 | 5 | 11 ³ / ₄ | 20 ³ / ₄ | 10 | 19 | 4 ³ / ₄ | 1/2 | Yes | 3002, 3005, 3005-3, 3302, 3305, 3305-3 |
| | 7008 | 7038 | 7058 | 7078 | Semi-Recessed | 9 | 18 | 5 | 11 ³ / ₄ | 20 ³ / ₄ | 10 | 19 | 3 ¹ / ₄ | 2 | Yes | |
| | 7009 | 7039 | 7059 | 7079 | Surface | 11 ¹ / ₂ | 20 ¹ / ₂ | 6 | - | - | - | - | - | No | | |
| | 7010 | 7030 | 7050 | 7070 | Recessed | 9 | 24 | 5 | 11 ³ / ₄ | 26 ³ / ₄ | 10 | 25 | 4 ³ / ₄ | 1/2 | Yes | |
| | 7012 | 7032 | 7052 | 7072 | Semi-Recessed | 9 | 24 | 5 | 11 ³ / ₄ | 26 ³ / ₄ | 10 | 25 | 3 ¹ / ₄ | 2 | Yes | |
| | 7013 | 7033 | 7053 | 7073 | Semi-Recessed | 9 | 24 | 5 | 11 ³ / ₄ | 26 ³ / ₄ | 10 | 25 | 2 ¹ / ₄ | 3 | Yes | |
| | 7020 | 7040 | 7060 | 7080 | Recessed | 9 | 24 | 5 ³ / ₄ | 11 ³ / ₄ | 26 ³ / ₄ | 10 | 25 | 5 ¹ / ₂ | 1/2 | Yes | 3002, 3005, 3005-3, 3010, 3306, 3310, 3302, 3305, 3305-3, 3306, 3405 |
| | 7021 | 7041 | 7061 | 7081 | Trimless | 9 | 24 | 6 ¹ / ₄ | 12 ³ / ₄ | 27 ³ / ₄ | 10 | 25 | 6 ¹ / ₂ | - | Yes | |
| | 7022 | 7042 | 7062 | 7082 | Semi-Recessed | 9 | 24 | 5 ³ / ₄ | 11 ³ / ₄ | 26 ³ / ₄ | 10 | 25 | 4 | 2 | Yes | |
| | 7023 | 7043 | 7063 | 7083 | Semi-Recessed | 9 | 24 | 5 ³ / ₄ | 11 ³ / ₄ | 26 ³ / ₄ | 10 | 25 | 3 | 3 | Yes | |
| | 7024 | 7044 | 7064 | 7084 | Surface | 11 ¹ / ₂ | 26 ¹ / ₂ | 6 | - | - | - | - | - | No | | |
| | 7025 | 7045 | 7065 | 7085 | Recessed | 12 | 27 | 8 | 14 ³ / ₄ | 29 ³ / ₄ | 13 | 28 | 7 ³ / ₄ | 1/2 | Yes | 3020, 3202, 3320, 3410 |
| | 7026 | 7046 | 7066 | 7086 | Trimless | 12 | 27 | 8 ¹ / ₂ | 15 ³ / ₄ | 30 ³ / ₄ | 13 | 28 | 8 ³ / ₄ | - | Yes | |
| | 7027 | 7047 | 7067 | 7087 | Semi-Recessed | 12 | 27 | 8 | 14 ³ / ₄ | 29 ³ / ₄ | 13 | 28 | 5 ¹ / ₄ | 3 | Yes | |
| | 7028 | 7048 | 7068 | 7088 | Semi-Recessed | 12 | 27 | 8 | 14 ³ / ₄ | 29 ³ / ₄ | 13 | 28 | 3 ¹ / ₄ | 5 | No | |
| | 7029 | 7049 | 7069 | 7089 | Surface | 14 ⁵ / ₈ | 29 ³ / ₈ | 8 | - | - | - | - | - | No | | |

ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE NOTED

Job Name: _____

Architect/Contractor: _____

Rep: _____

Page: _____ of _____

DATE:
January 2009

MODEL NUMBER
7007-7089 SERIES



FIRE RATED 7000 SERIES FIRE EXTINGUISHER CABINETS UL CLASSIFIED, 7N43

REGULARLY FURNISHED:

BOX- Cold rolled steel with an electrostatically applied, thermally-fused polyester coating with recoatable white finish, and a continuous hinge.

DOOR AND FRAME


7007-7028 Series: Steel - Cold rolled steel with recoatable white polyester finish.

7030-7048 Series: Aluminum - Satin finish, clear polyester coated.

7050-7068 Series: Stainless Steel - #304 Stainless Steel with #4 finish.

7070-7088 Series: Brass - Polished finish, clear polyester coated.

Wall mounting and size of cabinet as selected by model number.



| Qty | Model No. | | | | Wall Mounting | Inside Box Dimensions | | | Overall Frame | | Minimum Wall Opening Required | | | Trim | ADA | For Use With These Extinguishers |
|-----|-----------|----------|-----------------|-------|---------------|-----------------------|----|-------------------------------|--------------------------------|--------------------------------|--------------------------------|----|-------------------------------|------|-----|----------------------------------|
| | Steel | Aluminum | Stainless Steel | Brass | | K | L | M | N | O | W | H | D | | | |
| | 7007 | 7037 | 7057 | 7077 | Recessed | 9 | 18 | 5 | 11 ³ / ₄ | 20 ³ / ₄ | 11 ¹ / ₄ | 20 | 5 ⁵ / ₈ | 1/2 | Yes | 3002 |
| | 7008 | 7038 | 7058 | 7078 | Semi-Recessed | 9 | 18 | 5 | 11 ³ / ₄ | 20 ³ / ₄ | 11 ¹ / ₄ | 20 | 4 ¹ / ₈ | 2 | Yes | 3005 |
| | 7010 | 7030 | 7050 | 7070 | Recessed | 9 | 24 | 5 | 11 ³ / ₄ | 26 ³ / ₄ | 11 ¹ / ₄ | 26 | 5 ⁵ / ₈ | 1/2 | Yes | 3005-3 |
| | 7012 | 7032 | 7052 | 7072 | Semi-Recessed | 9 | 24 | 5 | 11 ³ / ₄ | 26 ³ / ₄ | 11 ¹ / ₄ | 26 | 4 ¹ / ₈ | 2 | Yes | 3302 |
| | 7013 | 7033 | 7053 | 7073 | Semi-Recessed | 9 | 24 | 5 | 11 ³ / ₄ | 26 ³ / ₄ | 11 ¹ / ₄ | 26 | 3 ¹ / ₈ | 3 | Yes | 3305 |
| | 7020 | 7040 | 7060 | 7080 | Recessed | 9 | 24 | 5 ³ / ₄ | 11 ³ / ₄ | 26 ³ / ₄ | 11 ¹ / ₄ | 26 | 6 ³ / ₈ | 1/2 | Yes | 3305-3 |
| | 7021 | 7041 | 7061 | 7081 | Trimless | 9 | 24 | 6 ¹ / ₄ | 12 ³ / ₄ | 27 ³ / ₄ | 11 ¹ / ₄ | 26 | 7 ³ / ₈ | - | Yes | 3006 |
| | 7022 | 7042 | 7062 | 7082 | Semi-Recessed | 9 | 24 | 5 ³ / ₄ | 11 ³ / ₄ | 26 ³ / ₄ | 11 ¹ / ₄ | 26 | 4 ⁷ / ₈ | 2 | Yes | 3010 |
| | 7023 | 7043 | 7063 | 7083 | Semi-Recessed | 9 | 24 | 5 ³ / ₄ | 11 ³ / ₄ | 26 ³ / ₄ | 11 ¹ / ₄ | 26 | 3 ⁷ / ₈ | 3 | Yes | 3306 |
| | 7025 | 7045 | 7065 | 7085 | Recessed | 12 | 27 | 8 | 14 ³ / ₄ | 29 ³ / ₄ | 14 ¹ / ₄ | 29 | 8 ⁵ / ₈ | 1/2 | Yes | 3310 |
| | 7026 | 7046 | 7066 | 7086 | Trimless | 12 | 27 | 8 ¹ / ₂ | 15 ³ / ₄ | 30 ³ / ₄ | 14 ¹ / ₄ | 29 | 9 ⁵ / ₈ | - | Yes | 3405 |
| | 7027 | 7047 | 7067 | 7087 | Semi-Recessed | 12 | 27 | 8 | 14 ³ / ₄ | 29 ³ / ₄ | 14 ¹ / ₄ | 29 | 6 ¹ / ₈ | 3 | Yes | 3020 |
| | 7028 | 7048 | 7068 | 7088 | Semi-Recessed | 12 | 27 | 8 | 14 ³ / ₄ | 29 ³ / ₄ | 14 ¹ / ₄ | 29 | 4 ¹ / ₈ | 5 | No | 3202 |
| | | | | | | | | | | | | | | | | 3320 |
| | | | | | | | | | | | | | | | | 3410 |

ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE NOTED

Job Name: _____
 Architect/Contractor: _____
 Rep: _____
 Page: _____ of _____

DATE:
January 2009

MODEL NUMBER
FRC7007-FRC7088 SERIES