



SPEC SHEET

POSIGRIP HVY713SUTS TOUCH SCREEN HI VIS YELLOW PU PALM COATED NYLON GLOVES

Hi vis yellow nylon shell with grey polyurethane palm coating for enhanced tactile sensitivity and high level of dexterity. Touch screen fingertips.

FEATURES

- Conductive threads in finger tips for use with touch screens.
- Knit wrist, machine washable
- Polyurethane coating
- EN388 = 4131

APPLICATIONS

- Bottling and Canning
- Recycling
- Manufacturing
- Assembly

SPEC DETAILS

COLOR DETAIL	Hi-Vis Yellow: Pantone 387 U; Gray: Pantone 15-6304 TPX
COATING	PU
CUFF STYLE	Knit Wrist

TEST STANDARDS

- EN388 = 4131

SIZES

XSmall, Small, Medium, Large, XLarge, 2XLarge

DIMENSIONS

ITEM SIZE	GLOVE LENGTH	PALM WIDTH	HEM COLOR
XSmall	8.5"	3.25"	Yellow
Small	9"	3.5"	Red
Medium	9.5"	3.75"	Green
Large	10"	4.0"	Brown
XLarge	10.5"	4.25"	Blue
2XLarge	11"	4.5"	Black



PACKING INFO

PACKAGING	1 Units Per Pack, 25 Units Per Case		
ITEM	PAIR UPC	INNER PACK GTIN	MASTER PACK GTIN
HVY713SUTS/XS	662909138750	20662909138754	10662909138757
HVY713SUTS/S	662909500816	20662909500810	10662909500813
HVY713SUTS/M	662909500823	20662909500827	10662909500820
HVY713SUTS/L	662909500830	20662909500834	10662909500837
HVY713SUTS/XL	662909500847	20662909500841	10662909500844
HVY713SUTS/2XL	662909500854	20662909500858	10662909500851

PACKAGING DIMENSIONS AND WEIGHTS			
ITEM	PC WEIGHT (LBS)	MASTER PACK (IN)	MASTER PACK (LBS)
HVY713SUTS/XS	0.908	28 x 11.25 x 13.5	23.7
HVY713SUTS/S	0.908	28 x 11.25 x 13.5	23.7
HVY713SUTS/M	0.93	28.5 x 11 x 13.5	24.25
HVY713SUTS/L	0.912	23.2 x 10.6 x 19.3	23.8
HVY713SUTS/XL	0.97	23.2 x 11 x 19	25.25
HVY713SUTS/2XL	1.02	23.2 x 11 x 19	26.5
COUNTRY OF ORIGIN	China		

1.800.647.1900

WESTCHESTERGEAR.COM

© 2018 WEST CHESTER PROTECTIVE GEAR

The West Chester Protective Gear Shield is a trademark of West Chester Protective Gear