

HIGH TRACTION ALUMINUM DOCK PLATE

Diamond tread surface provides more traction points per square foot than competitor's surface. Lightweight $\frac{3}{8}$ " thick aluminum withstands heavy traffic but lifts easily using handholds. The 11" apron with beveled edges and an 11° crown provide smooth, efficient entry and exit. Bottom includes a bolted safety stop to keep plate in position. **Note** that width should be 12" wider than load. Not for use with rider type trucks.

Model	W"x L"	Ht.**	Cap. Lbs.	Wt. Lbs.	Price
FD241742	36 x 24	1	3350	35	\$189.00
FD241743	36 x 36	3	2000	46	266.95
FD241744	48 x 24	1	3700	51	253.95
FD241745	48 x 36	3	2700	66	329.95
FD241746	48 x 48	5	2050	86	405.95
FD241747	60 x 48	5	2660	100	495.95

*Height is the difference above or below dock.


HIGH VISIBILITY SAFETY YELLOW

AS LOW AS
\$189

MEETS OSHA SPEC. NO. 1910.30(A)

SAME DAY IN STOCK SHIPMENT

SAFETY STOP
CONVENIENCE HANDLE



HEAVY DUTY ALUMINUM DOCK PLATE

Lightweight aluminum dock plate has integral handle holes for easy lifting and slip-resistant diamond tread surface. Beveled entry and exit edges, 11" apron and 11° crown angle offer smooth transition between truck and dock. Safety stop underneath helps secure plate in position. Not for use with rider type trucks. Note that width should be 12" wider than load.

Model	W"x L"	Ht.**	Cap. Lbs.	Wt. Lbs.	Price
$\frac{3}{8}$" THICK PLATE - STANDARD DUTY					
FD244340	36 x 24	1	4720	47	\$214.00
FD244342	36 x 36	3	3238	64	295.95
FD244344	36 x 48	5	1764	79	377.95
FD244346	48 x 24	1	6210	58	280.95
FD244348	48 x 36	3	4383	79	364.95
FD244350	48 x 48	5	2388	99	449.95
FD241172	48 x 60	7	1656	118	533.00
FD244352	60 x 48	5	3158	114	548.00
FD244354	60 x 60	7	2414	145	659.00
$\frac{1}{2}$" THICK PLATE - HEAVY DUTY					
FD244353	48 x 24	1	9079	65	348.95
FD241173	48 x 30	2	8067	77	413.95
FD244355	48 x 36	3	6265	93	465.95
FD244356	48 x 48	5	4532	122	593.00
FD244358	60 x 48	5	4268	152	714.00

*Height is the difference above or below dock.




CONVENIENCE HANDLE

SLIP-RESISTANT DIAMOND PLATE

LIGHTWEIGHT... CUT LOADING COSTS AND HAZARDS - DESIGNED TO MEET OSHA SPEC. NO. 1910.30(A) AND ANSI MH30.2

AS LOW AS
\$214

SLIP-RESISTANT DIAMOND PLATE



SAFETY STOP

ALUMINUM WHEEL RISER

Skidproof for Safer Loading and Unloading

These heavy duty ramps make it easy to bring a truck or trailer into your dock at a smooth working level. Constructed of rugged lightweight aluminum with non-skid safety tread for fast and safe loading and unloading. 15,000 lb. capacity per ramp. Ramps sold individually.

Model	Level Ramp H" L"	Overall L" W"	Wt. Lbs.	Price Each
FD247360	6 30 18	48 18	72	\$394.00
FD247362	6 30 18	48 24	89	462.95
FD247364	8 30 24	54 18	93	452.95
FD247366	8 30 24	54 24	111	557.00
FD247368	10 30 30	60 18	115	547.00
FD247370	10 30 30	60 24	136	643.00
FD247372	12 36 36	72 18	160	691.00
FD247374	12 36 36	72 24	188	816.00

AS LOW AS


\$394

30,000 lb. capacity per pair



EDGE-OF-DOCK LEVELER

Attaches easily to steel nosing of existing dock, saving valuable dock loading space; no concrete work or pit necessary. All models have a 5" upward and 5" downward working range. A full 15" lip projects 12" beyond bumper. High strength $\frac{3}{8}$ " steel safety plate. Heavy duty hinges. Automatically releases and returns to stored position when truck exits. **MECHANICAL MODEL:** counter-balanced extension spring lift to ensure one person, one hand operation. Includes 41" L steel hook to facilitate opening of leveler. **POWERED MODEL:** push button control operates the 115V $\frac{1}{2}$ HP motor which raises and lowers, extends and retracts leveler for easy operation. Independent hydraulic cylinders on both lip and center plate provide descent control. Both models supplied with two 12" x 14" molded rubber bumpers and reinforced mounting blocks.



MECHANICAL MODEL

Model	Lip W" x D"	Overall Width"	Price
FD390200	66 x 27 $\frac{3}{4}$	102	\$749.00
FD390202	72 x 27 $\frac{3}{4}$	108	799.00

AS LOW AS
\$749

20,000 lb. capacity

POWERED MODEL

Model	Lip W" x D"	Overall Width"	Price
FD390203	66 x 30	104	\$2199.00
FD390204	72 x 30	110	2399.00

Visit globalindustrial.com for Pit Mount Dock Levelers



1-800-645-1232

globalindustrial.com

229