



# STEEL DECK TRUCK

## All Welded Construction

All welded heavy duty 14 gauge steel decks, reinforced with internal longitudinal stiffening members for extra strength. **Non-marring integral corner bumpers protect walls.** Removable pipe handle. Bolt-on casters are double ball race, two swivel and two rigid. Durable baked gray enamel finish. 5" dia. wheels offer 7 1/2" deck height, 6" dia. have 8 1/2" height and 8" dia. have 10 3/4" height. **Optional Ergo Handle helps to reduce strain on the back, wrists and arms. Specify Ergo suffix (E) to any model and add \$30.00 to list price.**

AS LOW AS  
**\$124**

**2400 lb. capacity**

SAME DAY  
**IN STOCK**  
SHIPMENT

Online  
Video  
& Photos




SHOCK-ABSORBING  
PNEUMATIC  
WHEELS

PROTECTIVE  
BUMPERS

FD952112P

EXCLUSIVE BETTER BUILT  
CHANNEL REINFORCED DECK



OPTIONAL ERGO HANDLE

Deck L" x W"	Model	1-11	12-24	25+	Price Each
<b>5" x 1 1/4" POLYURETHANE WHEELS 1000 LB. CAP.</b>					
36 x 24	FD952105	\$136.95	\$131.00	\$124.00	
48 x 24	FD952106	157.95	151.00	144.00	
48 x 30	FD952107	174.95	167.00	159.00	
60 x 30	FD952108	206.95	197.00	188.00	
72 x 36	FD952109	251.95	240.00	228.00	
<b>5" x 1 1/2" RUBBER TIRED WHEELS 1400 LB. CAP.</b>					
36 x 24	FD952110	151.95	145.00	138.00	
48 x 24	FD952112	172.95	165.00	157.00	
48 x 30	FD952113	189.95	181.00	172.00	
60 x 30	FD952116	221.95	211.00	201.00	
72 x 36	FD952118	266.95	254.00	242.00	
<b>6" x 2" RUBBER TIRED WHEELS 2000 LB. CAP.</b>					
36 x 24	FD952121	161.95	154.00	147.00	
48 x 24	FD952123	182.95	174.00	166.00	
48 x 30	FD952122	199.95	190.00	181.00	
60 x 30	FD952127	231.95	221.00	210.00	
72 x 36	FD952129	276.95	264.00	251.00	
<b>8" x 2" RUBBER TIRED WHEELS 2400 LB. CAP.</b>					
36 x 24	FD952130	176.95	169.00	161.00	
48 x 24	FD952132	197.95	189.00	180.00	
48 x 30	FD952139	214.95	205.00	195.00	
60 x 30	FD952136	246.95	235.00	224.00	
72 x 36	FD952138	291.95	278.00	265.00	
<b>8" x 2 1/2" FULL PNEUMATIC SHOCK-ABSORBING WHEELS 1200 LB. CAP.</b>					
36 x 24	FD952110P	226.95	216.00	206.00	
48 x 24	FD952112P	247.95	235.00	224.00	
48 x 30	FD952113P	264.95	252.00	240.00	
60 x 30	FD952116P	296.95	283.00	269.00	
72 x 36	FD952118P	341.95	325.00	309.00	



FD241536

AS LOW AS  
**\$309**

# STAINLESS STEEL DECK TRUCK

**1200 lb. capacity**

All welded stainless steel truck is perfect for use in corrosive applications at labs, restaurants and hospitals. Premium 16 gauge #4 polished deck and 14 gauge caster mounts for years of service. Rolls smoothly on 2 swivel, 2 rigid casters. 5" wheels offer 8" deck height while 8" wheels have 12" height. Comfortable removable stainless steel push handle.

Deck L" x W"	5" x 1 1/4" POLYURETHANE WHEELS 1200 LB. CAP.		8" x 3" FULL PNEUMATIC WHEELS 1200 LB. CAP.	
	Model	Price	Model	Price
36 x 18	FD241535	\$309.00	FD241539*	\$398.95
36 x 24	FD241536	334.95	FD241540	424.95
48 x 24	FD241537	359.95	FD241541	449.95
60 x 30	FD241538	454.95	FD241542	545.00

\*Semi-Pneumatic Wheels

# ALUMINUM DECK TRUCK

**Lightweight, Maintenance Free - 2400 lb. capacity**

Maximum strength, lightweight deck makes this the perfect choice for moving bulk product. All-welded aluminum channel frame and deck ensures long life and resists corrosion. Slip-resistant diamond tread deck surface has more grip cleats per square foot than competitive trucks, helping to prevent items from falling during transport. **Non-marring integral corner bumpers protect walls.** Newly designed offset ergonomic aluminum push handle helps reduce fatigue and increases maneuverability. Reinforced corner sockets on both ends allows use of additional push handle (sold separately). Rolls smoothly on 2 swivel, 2 rigid roller bearing wheels. 5" dia. wheels offer 7 1/2" deck height, 6" dia. have 8 1/2" height and 8" dia. have 10 3/4" height.

AS LOW AS  
**\$279**

ALUMINUM  
HANDLE



NON-SLIP  
DIAMOND  
TREAD

Deck L" x W"	5" x 1 1/4" POLYURETHANE WHEELS 1000 LB. CAP.		5" x 1 1/2" RUBBER TIRED WHEELS 1400 LB. CAP.		6" x 2" RUBBER TIRED WHEELS 2000 LB. CAP.		8" x 2" RUBBER TIRED WHEELS 2400 LB. CAP.		8" x 2 1/2" FULL PNEUMATIC WHEELS 1200 LB. CAP.	
	Model	Price	Model	Price	Model	Price	Model	Price	Model	Price
48 x 24	FD241549	\$279.00	FD241550	\$293.95	FD241551	\$303.95	FD241552	\$318.95	FD241553	\$368.95
48 x 30	FD232596	312.95	FD232600	327.95	FD232610	337.95	FD232620	352.95	FD232630	402.95
60 x 30	FD232597	345.95	FD232602	360.95	FD232612	370.95	FD232622	385.95	FD232631	435.95
56 x 42	FD241590	459.95	FD241591	474.95	FD241592	484.95	FD241593	499.95	FD241594	550.00



FD241553

FREE  
PROTECTIVE  
BUMPERS



SAME DAY  
**IN STOCK**  
SHIPMENT



FD241593

**56" L x 42" W  
Pallet Sized!**

ADDITIONAL REMOVABLE  
ALUMINUM HANDLE

Model	Deck Width"	Price
FD241554	24	\$29.95
FD241555	30	33.95
FD241595	42	38.95

