

CONDUCTIVE GRID CONTAINERS

AS LOW AS
\$7.10

DIVIDERS



FD334203

Injection molded with a carbon filled copolymer polypropylene, which protects sensitive electronic components from typical electromagnetic interference (EMI). **Electrostatic Decay Rate is tested to meet Mil Spec Mil-B-81075B at less than 0.1 seconds. Surface resistivity is less than 105 Ohms/Sq. when tested per ASTM-D257.** Sold in carton quantities. Dividers are conductive black. Dividers and label holders sold in packages of 6.

DIVIDABLE GRID CONTAINERS

Dividable to 1 1/8" Square
Available in Standard
or Conductive.



CLEAR COVER

DIVIDER

FD334103RD

AS LOW AS
\$3.65

STANDARD GRID CONTAINERS



COVER

DIVIDER

OPTIONAL LABEL HOLDER

FD334101BL

48 HOUR SHIPMENT


Heavy-Duty Dividable Grid Containers can be used in industrial, commercial, electronic and health care industries for storage, assembly, fabrication and distribution applications. These containers offer the safest and most efficient method of compartmentalizing and protecting all kinds of small to medium size parts allowing you to customize the container interior for your exact needs. Molded-in stacking ridge assures containers will **stack securely with or without covers**. Containers are designed to maximize space in storage and transportation. Compatible with most racks, shelving and automated, material handling equipment, stacking rims and multi-ribbed external sides provide high impact strength. Large, smooth surface area on all four sides for content identification. Optional **clear, plastic label holder** attaches securely with Velcro® Brand fasteners to any size container (available in 3 sizes). Containers can be divided by length and/or width allowing subdivision down to a 1 1/8" square compartment size. **STANDARD GRID CONTAINERS** are available in 9 sizes and 3 colors: Blue, Gray and Red. **Injection molded from high density FDA approved polyethylene** which resists most solvents and chemicals. Snap on clear or same colored covers protect content from damage or dust in shipping and storage. *Add Color Suffix: Blue (BL), Gray (GY) or Red (RD). Containers and Covers sold in carton quantities. Dividers are gray. Dividers and Label Holders sold in packages of 6.

Outside L" x W" x H	Carton Qty.	Cap. Lbs.	BOX		LENGTH DIVIDER				WIDTH DIVIDER					
			STANDARD*		CONDUCTIVE		STANDARD		CONDUCTIVE		STANDARD		CONDUCTIVE	
Model	Price Each	Model	Price Each	Model	Price/6 pkg.	Model	Price/6 pkg.	Model	Price/6 pkg.	Model	Price/6 pkg.	Model	Price/6 pkg.	
10 7/8 x 8 1/4 x 3 1/2	20	25	FD334100	\$3.65	FD334203	\$7.10	FD334109	\$3.94	FD334212	\$7.20	FD334118	\$3.55	FD334221	\$5.70
10 7/8 x 8 1/4 x 5	20	25	FD334101	4.39	FD334204	8.30	FD334110	4.10	FD334213	8.70	FD334119	3.65	FD334222	6.70
16 1/2 x 10 7/8 x 3 1/2	12	25	FD334102	5.30	FD334205	9.70	FD334111	5.00	FD334214	10.50	FD334120	4.10	FD334223	7.20
16 1/2 x 10 7/8 x 6	8	35	FD334103	6.90	FD334206	12.25	FD334112	8.80	FD334215	14.50	FD334121	6.10	FD334224	11.50
16 1/2 x 10 7/8 x 8	8	40	FD334104	8.80	FD334207	15.50	FD334113	9.30	FD334216	20.25	FD334122	7.70	FD334225	15.00
22 1/2 x 17 1/2 x 3	6	25	FD334105	8.50	FD334208	21.75	FD334114	9.50	FD334217	16.75	FD334123	8.70	FD334226	14.50
22 1/2 x 17 1/2 x 6	3	35	FD334106	11.00	FD334209	24.95	FD334115	10.25	FD334218	19.50	FD334124	9.30	FD334227	16.75
22 1/2 x 17 1/2 x 8	3	40	FD334107	14.50	FD334210	29.95	FD334116	11.25	FD334219	24.25	FD334125	10.25	FD334228	19.25
22 1/2 x 17 1/2 x 12	3	60	FD334108	19.00	FD334211	34.95	FD334117	23.50	FD334220	42.95	FD334126	21.25	FD334229	38.95

Outside L" x W" x H	Carton Qty.	COVER CLEAR		CONDUCTIVE		LABEL HOLDER Carton Qty.	STANDARD		CONDUCTIVE				
		Model	Price Ea.	Model	Price Ea.		Model	Price/6 pkg.	Model	Price/6 pkg.			
10 7/8 x 8 1/4	10	FD334127	\$2.39	FD334127CL	\$3.62	FD334230	\$4.70	8 x 2	6	FD334130	\$12.25	FD652710	\$13.25
16 1/2 x 10 7/8	4	FD334128	3.30	FD334128CL	5.60	FD334231	8.60	5 x 3	6	FD334131	13.25	FD652711	14.00
22 1/2 x 17 1/2	3	FD334129	5.60	FD334129CL	9.30	FD334232	15.00	8 x 5	6	FD334132	13.50	FD652712	14.50

*Add Color Suffix: (BL) Blue, (GY) Gray or (RD) Red.

AKRO-MILS



STACKABLE PLASTIC GRID BOXES

Helps organize small parts easily and efficiently. Injection molded high density polyethylene resists most solvents and chemicals. Ribbed sides provide rigidity when loaded or stacked. Divides into 1 1/8" square compartments using **Optional Black Plastic Dividers** (sold separately). Allows stacking with or without **Optional Clear Lids** (sold separately). Sold in carton quantities. Specify color suffix: Gray (GY), Blue (BL) or Red (RD).

Outside L" x W" x H	Container	Carton Qty.	Price Each	Length Black Divider	6 pkg/ Price	Width Black Divider	6 pkg/ Price	Clear Lid	Carton Qty.	Price Each
16 1/2 x 10 7/8 x 4	FD334278	12	7.00	FD334286	10.50	FD334294	7.80	FD257702	4	6.40
16 1/2 x 10 7/8 x 6	FD334279	8	9.20	FD334287	10.75	FD334295	8.80	FD257702	4	6.40
16 1/2 x 10 7/8 x 8	FD334280	6	10.50	FD334288	12.75	FD334296	9.50	FD257702	4	6.40
22 3/8 x 17 3/8 x 4	FD334281	6	11.75	FD334289	13.25	FD334297	11.40	FD257703	3	10.25
22 3/8 x 17 3/8 x 6	FD334282	4	13.75	FD334290	22.50	FD334298	18.75	FD257703	3	10.25
22 3/8 x 17 3/8 x 8	FD334283	3	17.75	FD334291	19.00	FD334299	16.75	FD257703	3	10.25
22 3/8 x 17 3/8 x 10	FD334284	2	20.25	FD334292	15.75	FD334300	12.50	FD257703	3	10.25

1-800-645-1232

globalindustrial.com

23