


# Ergo cordless Backpack Vac by Atrix

**ERGO**  
by Atrix™

cordless



VACBP36V

## **WARRANTY**

1 Year Limited

## **CORD FREE**

Safe, Cordless, Convenient, Easily Convertible  
(Left Hand/Right Hand)

## **ERGONOMIC**

LOW PROFILE

## **POWERFUL VACUUM AND BLOWER**

500 Watt Cleaning Power, Long 55 Minute Run Time,  
Quick 3 Hour Charge

## **SAFE**

4 levels of Filtration with 8 Quart HEPA Bag  
\*not for hazardous particles

## **APPLICATIONS**

JAN/SAN, Offices, Warehouses, Stairs, Ceilings, Entryways,  
Scaffolding, Crawl Spaces



# Ergo cordless Backpack Vac by Atrix

## SPECIFICATIONS

### VACBP36V

#### DIMENSIONS

Length: 12" (305 mm)

Width: 10" (254 mm)

Height: 23" (584 mm)

**WEIGHT** 18.5 lbs. (8.41 kg)

#### HOSE DIAMETER

Inside – 1.13" (28.7 mm)

Outside – 1.38" (35 mm)

#### POWER

36v 500W

#### CFM

71 CFM

## INCLUDED CONTENTS

- A – Ergo cordless Backpack Vacuum/ Blower by Atrix
- B – BP4 - 6' Hose
- C – BP17 - Blower Adapter (not shown)
- D – BP18 - Exhaust Filter Cover
- E – BP39 - Extension Wand, 22"-37"
- F – BP45 - Set of 3 Blower Nozzles
- G – BP40 - Furniture Nozzle
- H – BP41 - Crevice Tool
- I – BP42 - Round Brush
- J – BP43-1 - Floor Brush
- K – BP44 - Air Driven Turbo Brush

## FILTRATION

### 4 Stage

### 8 Quart HEPA Bag

### Cloth Shakeout Bag

### HEPA Premotor Filter

### Exhaust Filter

- L – VACBP6 - Hepa Bag
- M – VACBP8 - Shakeout Bag (not shown)
- N – BPFILPACK - Premotor and Exhaust Filter Set
- O – BPBAT - 36V Lithium Ion Battery
- P – BPCHG - Charger w/3 Cords: USA, Euro, UK



## GENERAL INFORMATION

### Packaging

Dimensions:	L	W	H
Inches:	34	14	13
mm:	864	356	330
Weight:	34 lbs. 15.54 kg		

### HS Code

8508.11.0000

### UPC

8 38067 00072 1

## OPTIONAL ACCESSORIES

### Hepa Vacuum Bags 10 pack – VACBP6-10P



### Storage Bag – BP200



### Backpack Series Replacement Battery – BPBAT

