

Explosion Proof Spider Box - Four 15 Amp 120 Volt Explosion Proof Outlets

Part #: EPL-4X0-SBO

**Made in the USA**

The Larson Electronics EPL-4X0-SBO explosion proof spider box offers four 120volt outlets. Optional configurations include 120 VAC in . This portable explosion proof spider box is ideal for powering explosion proof lights or related equipment.

****PLEASE NOTE: ANY FREE SHIPPING OFFERS DO NOT APPLY TO POWER DISTRIBUTION PANELS, TRANSFORMERS, OR SUBSTATIONS****

The EPL-TX-200-4X120 explosion proof portable transformer from Larson Electronics is built to provide operators in hazardous locations with a method of stepping down single phase high primary voltages to safe and reliable 120 VAC 50/60hz current or low voltage 12 or 24 Volt AC or DC output. This unit includes four explosion proof receptacles rated at 20 amps each. This compact power distribution system is designed for portability and convenience as well as durability and is mounted to a wheeled, non-sparking aluminum frame for added protection.

This portable step down transformer features four Class 1 & 2 Division 1 and 2 receptacles with twist lock operation to provide protection against sparking in hazardous environments. The four outlets and standard output voltages of this step down transformer make it a popular choice for operating our 100 watt explosion proof drop lights and work lights. Overseas operators will find this unit ideal for converting their higher European and overseas voltages to common standard American voltages when operating American equipment.

The output side is equipped with four 2023, Class 1, Division. 1 receptacles designed to accept twist lock plugs like our EPP-15A and EPP-20A explosion proof plugs. This power transformer is rated at 500VA, and comes standard with a 25 foot primary power cord equipped with a 20amp, 220v explosion proof male plug. Choose your primary input and secondary output voltages below when ordering.

Larson Electronics.com can build transformers to your specifications. If this model does not meet your needs, please contact us at 1-800-369-6671 or sales@larsonelectronics.com.

Specifications / Additional Information

EPL-TX-200-4X120 Explosion Proof Power Transformer

Line In: 220/240VAC 50/60hz

Line Out: 4- 2023, Class 1, Div. 1 Receptacles 120VAC 50/60hz OR 12V / 24V AC or DC

Wiring: 25' SOOW with 20amp, 220v Plug

Dimensions: 30"-H x 14"-D x 24"- W

Weight: 105lbs

Mounting: Portable Dolly Cart with Wheels

Ratings: Class 1 Division 1 Explosion Proof

VA: 500

Features/Ratings

Class 1 Division 1 Explosion Proof

2023, Class 1, Division. 1 Receptacles

20 Amp Primary Rating

Special Orders- Requirements

Contact us for special requirements

Toll Free: 1-800-369-6671

Intl: 1-903-498-3363

E-mail: sales@larsonelectronics.com

All grounding shall comply with state and local codes and meet the minimum requirements of the National Electronic Code section 250

[Scroll Down to Purchase](#)

[Part #: EPL-4X0-SBO \(68856\)](#)







Links (Click on the below items to view):

- [Hi-Res Image 1](#)
- [Hi-Res Image 2](#)
- [Hi-Res Image 3](#)
- [Hi-Res Image 4](#)

- Hi-Res Image 5