



GAS CYLINDER HEATERS

Powerblanket

Powerblanket® has the best gas cylinder heaters on the market. Our heating blankets will overcome the effects of cold weather and maintain pressure and efficiency on any gas cylinder.

powerblanket
patented technology



WHY CHOOSE POWERBLANKET GAS CYLINDER HEATERS?

- Increase performance and efficiency of gas cylinders
- Save money by optimizing gas and material usage
- Eliminate unnecessary cylinder refills in cold weather
- Insulated full-wrap design
- UL/CSA/CE safety certifications





OUR CUSTOMERS LOVE US

A large US railroad company that uses these heaters is able to keep snow off the tracks by applying the Powerblanket® Gas Cylinder Warmers to their 1000 lb propane tanks which power their generators along the railway system. Before using the Powerblanket® heaters, the cold temperatures kept the propane from vaporizing, which meant there was not enough pressure in the tank to run the generators.

POWERBLANKET TECHNICAL SPECS GAS CYLINDER



CERTIFIED TO UL/CSA/CE STANDARDS
CONFORMS TO ANSI/UL STD 499
CERTIFIED TO CAN/CSA C22.2 NO 130
CID2-T4 FOR HAZARDOUS LOCATIONS AVAILABLE

Powerblanket Model #	Container Volume Size	Product Temperature	Blanket Dimensions	Voltage	Wattage (+-5%)	Amps (+-5%)	Weight
PRO Model							
GCW20 (20lb)	12.5"Dx18"H / 32cmx46cm	90° ± 10° F / 32° C ± 5° C	20"x45" / 51cm x 114cm	120V	120	1.00	4 lbs / 2 kg
GCW30 (30lb)	12.5"Dx24"H / 32cmx61cm	90° ± 10° F / 32° C ± 5° C	26"x45" / 66cm x 114cm	120V	160	1.33	6 lbs / 3 kg
GCW40 (40lb)	12.5"Dx29"H / 32cmx74cm	90° ± 10° F / 32° C ± 5° C	33"x45" / 84cm x 114cm	120V	280	2.33	8 lbs / 4kg
GCW100 (100lb)	14.5"Dx48"H / 37cmx122cm	90° ± 10° F / 32° C ± 5° C	50"x52" / 127cm x 132cm	120V	550	4.58	12 lbs / 6 kg
GCW420 (420lb)	30"Dx52"H / 76cmx132cm	90° ± 10° F / 32° C ± 5° C	53"x104" / 135cm x 264cm	120V	960	8.00	18 lbs / 8 kg

Powerblanket® does custom projects too. Other sizes, voltage requirements, and heating requirements are available upon request.

Call us for a quote on a custom container heater that fits your specific needs.