



The WBZ washdown retail scale is ideally suited for food preparation, outdoor markets, shops and agriculture facilities. With a streamlined design, the WBZ fits neatly on crowded counters or workbenches. WBZ features a stainless steel pan and an IP66-rated washdown housing for protection against dust and water. The easy-to-read backlit display shows weight, price per unit, and an oversized view of the total cost. Completely portable, the WBZ operates with an AC adapter or rechargeable battery pack. With NTEP/Measurement Canada approvals, WBZ is suitable for use in trade.

**Portable and durable IP66-rated scale is a winner for price computing in retail locations**



## Features

- Vivid, backlit LCD easily visible in any lighting conditions
- Backlit LCD shows weight, unit price and total price, to provide all key information simultaneously
- Rear display mounted on the back of the scale lets customers see key data
- Color-coded keys facilitate quick recognition of the most frequently used buttons
- Heavy-duty rubber feet ensure stability of unit
- Large, grade 304 stainless steel pan allows swift cleaning
- Overload protection helps prevent damage to internal components
- Sealed keypad protects against dirt and spills
- Solid ABS housing is durable for industrial use
- External calibration allows for verification and adjustment with weights
- Preset tare function speeds the process of repetitive weighing
- Price displayed in choice of available currencies
- Security password control prevents unauthorized access
- Selectable auto-clear function enables the last item to be reset each time the scale returns to zero
- Switchable between price per kg and price per 100g or price per lb
- Zero-tracking feature ensures display returns to zero reading
- IP66-rated for protection against water and dust
- AC adapter included
- Rechargeable battery included for operation almost anywhere
- Programmable auto power-off to save energy

## Applications

- Weighing
- Price computing

## About ADAM:

For more than 40 years, professionals worldwide have relied on Adam Equipment for an extensive selection of dependable and affordable weighing equipment. Adam provides the right balance of speed, performance and value.

Model	WBZ 6a	WBZ 15a	WBZ 30a
<b>Capacity</b>	6lb / 3kg	15lb / 6kg	30lb / 15kg
<b>Readability</b>	0.002lb / 1g	0.005lb / 2g	0.01lb / 5g
<b>Repeatability (S.D.)</b>	0.002lb / 1g	0.005lb / 2g	0.01lb / 5g
<b>Linearity (+/-)</b>	0.004lb / 2g	0.01lb / 4g	0.02lb / 10g
<b>Pan Size</b>	8.3"x6.8" / 210x173mm		
<b>Weighing Units</b>	kg, lb		
<b>Stabilization Time (sec)</b>	2		
<b>Calibration</b>	External calibration		
<b>Display</b>	Backlit LCD with 0.6"/ 16mm -high digits		
<b>Power Supply</b>	12VDC 800mA adapter		
<b>Operating Temperature</b>	-10-10° to 40°C / 14° to 104°F		
<b>Housing</b>	ABS plastic		
<b>Overall Dim.</b>	9.1"x10.4"x6" / 231x265x153mm (wxdxh)		
<b>Net Weight</b>	7.3lb / 3.3kg		
<b>Approvals</b>	NTEP: 10-082A1 Measurement Canada: AM-5797C		

## Accessories

Item number	Description
303200002 .....	In-use wet cover (pack of 10)
303200003 .....	In-use wet cover (pack of 20)
303209190.....	In-use wet cover
700660290 .....	Calibration certificate
303147960 .....	Small scoop (complete with fitting to scales)
303147961 .....	Medium scoop (complete with fitting to scales)
303149759 .....	Vegetable Scoop (complete with fitting to scales)

## Key Accessories



**In-use cover**  
In-use covers provide an easy and affordable way to help keep the balance clean and protected.



**Vegetable Scoop**  
Metal scoops are designed to make portioning and food measurement easy. Three sizes available, small, medium and large.

## Supplied by