

# Heavy Duty Pan Racks

ITEM NO. \_\_\_\_\_  
 QUANTITY NO. \_\_\_\_\_  
 JOB NO. \_\_\_\_\_  
 SPEC NO. \_\_\_\_\_

## Specifications:

- For proofing, storage and transporting of 18" x 26" and 14" x 18" pans and trays.
- Heavy duty Aluminum or Stainless Steel frame with welded angle slides.  
Rolls easily on heavy duty 5" polyurethane swivel stem casters.
- Knock-down design offered on all aluminum models at no additional charge.
- Models AL-1818B and SS-1818B are designed for Roll-in Refrigerators.


## Options for Heavy Duty Pan Racks

Specify options by adding suffix to Model Numbers

- B** .....Bumpers (4)
- BP** .....Plate Casters with 4" rubber wheels
- LC** .....Locking Casters
- RTG-AL** .Removable Tray Guard/Aluminum
- RTS-SS** .Removable Tray Guard/Stainless Steel
- TG-AL** ...Tray Guard/Aluminum
- TG-SS** ...Tray Guard/Stainless Steel
- PU** .....Polyurethane Wheels
- KD** .....Knock-Down Design
- SB** .....Aluminum Solid Bottom

**1½" Wide Angle Slides Hold  
Trays Securely**

### Tray Direction



**AL-1830B**



**AL-1820B  
End Loading**



**1/2" Size  
Pan Racks  
AL-1810H  
End Loading**

### LABORATORY CERTIFICATION AND APPROVAL SYMBOLS:



Heavy Duty Pan Racks



439 Oak Street • Garden City, NY 11530 • Tel: 1-800-444-3595 • Fax: 516-222-0371  
[www.winholt.com](http://www.winholt.com) • [sales@winholt.com](mailto:sales@winholt.com)

NEW YORK • TEXAS • CALIFORNIA • MICHIGAN



ITEM NO. \_\_\_\_\_

JOB NO. \_\_\_\_\_

SPEC NO. \_\_\_\_\_

# Heavy Duty Pan Racks

Model Number	Ordering Number	Material	Tray Direction	Overall Dimensions						Pan Cap. 18"x26"	Space Bet. Runners		Approx. Ship Weight	
				Width		Length		Height			(in)	(mm)	(lb)	(kg)
				(in)	(mm)	(in)	(mm)	(in)	(mm)					
AL-1810B	109840	Aluminum	End Loading	21	533	26	660	69¾	1,772	10	6	152	35	16
SS-1810B	110470	Stainless Steel											80	36
AL-1812B	109882	Aluminum	End Loading	21	533	26	660	69¾	1,772	12	5	127	37	17
SS-1812B	110488	Stainless Steel											85	39
AL-1815B	109938	Aluminum	End Loading	21	533	26	660	69¾	1,772	15	4	102	41	19
AL-1818B	109989	Aluminum	End Loading	21	533	26	660	65	1,651	18	3	76	42	19
SS-1818B	110525	Stainless Steel											97	44
AL-1820B	110023	Aluminum	End Loading	21	533	26	660	69¾	1,772	20	3	76	48	22
SS-1820B	110541	Stainless Steel											110	50
AL-1830B	110120	Aluminum	End Loading	21	533	26	660	69¾	1,772	30	2	51	60	27
SS-1830B	110568	Stainless Steel											138	63
AL-2610B	110251	Aluminum	Side Loading	28	711	18	457	69¾	1,772	10	6	152	33	15
SS-2610B	110584	Stainless Steel											76	34
AL-2612B	110269	Aluminum	Side Loading	28	711	18	457	69¾	1,772	12	5	127	35	16
AL-2615B	110293	Aluminum	Side Loading	28	711	18	457	69¾	1,772	15	4	102	37	17
AL-2618B	110322	Aluminum	Side Loading	28	711	18	457	69¾	1,772	18	3	76	38	17
SS-2618B	156339	Stainless Steel											87	39
AL-2620B	110349	Aluminum	Side Loading	28	711	18	457	69¾	1,772	20	3	76	42	19
SS-2620B	110605	Stainless Steel											97	44
<b>Half Size Bun Pan Racks</b>														
AL-1806 / H	206797	Aluminum	End Loading	21	533	26	660	38	955	6	5	127	23	10
AL-1810 / H	206800	Aluminum								10	3	76	29	13
<b>Replacement Caster Information</b>														
757	123684	Swivel Square Stem Caster with 5" Polyurethane Wheel											—	
7112	122180	5" Polyurethane Wheel											—	

EXPRESS

Freight Class: 125

Win-Holt Equipment Group is a leading manufacturer of material & food handling equipment. Since 1946, retailers and restaurant chains have trusted Win-Holt's equipment to ensure increased productivity and efficiency in their operation. Multiple locations reduce logistics and transportation costs. All Win-Holt associates are dedicated to customer satisfaction.

For general sales and engineering information only. All units are subject to change without notice. Please consult factory for certified specifications.

439 Oak Street • Garden City, NY 11530 • Tel: 1-800-444-3595 • Fax: 516-222-0371  
 www.winholt.com • sales@winholt.com

NEW YORK • TEXAS • CALIFORNIA • MICHIGAN

Heavy Duty Pan Racks