



Ideal for industrial, agricultural, and food processing facilities, WBW scales feature IP66-rated washdown housing and a large stainless steel weighing pan. Precision load technology enables improved performance and greater efficiency during weighing and counting tasks. Checkweighing is simple, as the WBW's colour indicators alert the operator if a sample is under, over or within preset limits. Power is supplied by AC adapter or rechargeable battery, and auto power-off conserves battery life. WBW-M models are approved and suitable for use in trade.

Checkweighing is a breeze with the WBW's colour indicators



Features

- Vivid, backlit LCD easily visible in any lighting conditions
- Programmable backlight can be set to "always on," "always off" or "light only when weighing"
- Capacity tracker built into display for easily monitoring possible overloads
- Checkweighing LEDs clearly show under, over and acceptable limits
- Adjustable levelling feet help optimise setup
- Colour-coded keys facilitate quick recognition of the most frequently used buttons
- Large, grade 304 stainless steel pan allows easy cleaning
- Lightweight design simplifies transport and portability
- Solid ABS housing is durable for industrial use
- Overload protection helps prevent damage to internal components
- Audible overload alarm warns when capacity is exceeded
- External calibration allows for verification and adjustment with weights
- Simple operation allows quick startup and use with little or no training
- Zero-tracking feature ensures display returns to zero reading
- IP66-rated for protection against water and dust
- Rechargeable battery included for operation almost anywhere
- Programmable auto power-off to save energy
- AC adapter included

Applications

- Weighing
- Checkweighing

About ADAM:

For more than 40 years, professionals worldwide have relied on Adam Equipment for an extensive selection of dependable and affordable weighing equipment. Adam provides the right balance of speed, performance and value.

Model	WBW 5a	WBW 9a	WBW 18a	WBW 35a	WBW 6aM	WBW 15aM	WBW 30aM
Capacity	5lb / 2kg	9lb / 4kg	18lb / 8kg	35lb / 16kg	6lb / 3kg	15lb / 6kg	30lb / 15kg
Readability	0.0005lb / 0.2g	0.001lb / 0.5g	0.002lb / 1g	0.005lb / 2g	0.002lb / 1g	0.005lb / 2g	0.01lb / 5g
Repeatability (S.D.)	0.0005lb / 0.2g	0.001lb / 0.5g	0.002lb / 1g	0.005lb / 2g	0.002lb / 1g	0.005lb / 2g	0.01lb / 5g
Linearity (+/-)	0.001lb / 0.4g	0.002lb / 1g	0.004lb / 2g	0.01lb / 4g	0.004lb / 2g	0.01lb / 4g	0.02lb / 10g
Pan Size	8.3"x6.8" / 210x173mm						
Weighing Units	g, kg, lb, lb:oz						
Stabilisation Time (sec)	2						
Calibration	External calibration						
Display	Backlit LCD with 0.8"/ 20mm -high digits						
Power Supply	12VDC 800mA adapter / Internal rechargeable battery						
Operating Temperature	-10° to 40°C / 14° to 104°F						
Housing	ABS plastic						
Overall Dim.	9.1"x10.4"x6" / 231x265x153mm (wxdxh)						
Net Weight	7.3lb / 3.3kg						
Approvals	N/A				NTEP: 10-082A1 Measurement Canada: AM-5797C		

Accessories

Item number	Description
303200002	In-use cover (pack of 10)
303200003	In-use cover (pack of 20)
303209190	In-use cover
700660290	Calibration certificate
303147960	Small scoop (complete with fitting to scale)
303147961	Medium scoop (complete with fitting to scale)
303147959	Large scoop (complete with fitting to scale)

Key Accessories



In-use cover
In-use covers provide an easy and affordable way to help keep the balance clean and protected.



Large scoop
Metal scoops are designed to make portioning and food measurement easy. Three sizes available, small, medium and large.

Supplied by