

# LPS400

## Portable Shipping Scale CE



- **Accuracy**– 0.1% of full scale
- **Capacity**– 182 kg / 400 lb
- **Construction**– Low profile stainless steel platform with mild steel understructure, and stainless steel/ABS indicator with wall bracket and desk mount included.
- **Platform Dimension**–  
380 mm (L) x 305 mm (W) x 27 mm (H)  
15" W x 12" L x 1" H
- **Protocol**– Standard NCI interfaces to most common shipping software, including UPS™ Worldship Online.  
Not legal for trade
- **Display**– Five 16 mm / 0.625" digits LCD
- **Power**– Battery
- **Operator Keys**– On/Off/Zero, Tare, Units (lb/kg), Hold/Print

VALUE IN  
WEIGHING

# LPS400 Portable Shipping Scale

## Features

LPS400 scales are particularly suited to shipping and warehouse applications and general purpose weighing. These are very affordable scales with high accuracy.

A large, simple to read display can be wall or stand mounted for easy visibility (wall and desk bracket included).

The indicator cable is a coil style for durability and easy extension.

The LPS400 features RS-232 interface that can transmit and receive using a demand type protocol.

Scale comes standard with NCI protocol and interfaces to most common shipping software, including UPS™ Worldship Online.

A durable low profile platform allows for easy weighing. The LPS400 is a low cost yet versatile and portable scale.

- Application – Shipping/Receiving  
– Mailroom  
– Manifest Systems  
– General Purpose Weighing

Not legal for trade

## Specifications

### Capacity:

182 kg x 0.1 kg / 400 lb x 0.2 lb / 400 lb x 5 oz

**Display:** Five 16 mm / 0.625" digits LCD

**RS-232:** 10' interface cable (DB-9) (included)

**Keyboard:** On/Off/Zero, Tare, Units (kg/lb), Hold/Print

**Units:** lb, kg, lb/oz

**Power:** Four AAA batteries (included)



**Battery Life:** 20 hours

**Operating Temperature:** 5° C to 35° C / 41° F to 95° F

### Platform Dimension:

380 mm (L) x 305 mm (W) x 27 mm (H)  
15" W x 12" L x 1" H

### Indicator Dimension:

164 mm (L) x 81 mm (H) x 29 mm (W)  
6.5" L x 3.2" H x 1.2" W

**Product Weight:** 4 kg / 9 lb

### Packaging Dimension:

450 mm (L) x 400 mm (W) x 60 mm (H)  
17" L x 15" W x 2.3" H

**Shipping Weight:** 5 kg / 11 lb

**Certifications:** CE

**Product Code:** 816965006182



a division of Avery Weigh-Tronix, LLC

## Brecknell

1000 Armstrong Dr., Fairmont, MN 56031  
Toll free: 800-637-0529, Tel: 507-238-8702  
Fax: 507-238-8271  
e-mail: sales@brecknellscales.com  
www.brecknellscales.com



## Brecknell

Foundry Lane, Smethwick  
West Midlands B66 2LP UK  
Tel: +44 (0) 845 246 6717  
Fax: +44 (0) 845 246 6718  
Email: sales@brecknellscales.co.uk  
www.brecknellscales.co.uk

