

### Chrome Oxygen Cylinder Cart



Item #	For Use With	UOM
18143	12 C, D, E, or M9 Cylinders	1/cs
18144	20 C, D, E, or M9 Cylinders	1/cs

- Dual lifting handles.
- 5" Swivel casters, two with brakes.
- Chrome plated finish, alloy carbon steel.
- Module design saves on shipping.

**specifications**

Weight (18143   18144)	23.8 lbs.   28.7 lbs.
Length (18143   18144)	22.6"   27.6"
Width (18143   18144)	15.4"   20.5"
Height (18143   18144)	39.8"   39.8"
Warranty	Limited Lifetime

### Chrome Oxygen Cylinder Rack



Item #	For Use With	UOM
18140	20 C, D, E or M9 Cylinders	1/cs
18141	28 C, D, E or M9 Cylinders	1/cs

- Comes with bolt down feet.
- Chrome plated finish, alloy carbon steel.
- Reinforced double bar shelf frames.
- Modular design saves on shipping.
- Assists in OSHA compliance.

**specifications**

Weight (18140   18141)	18.7 lbs.   22.9 lbs.
Length (18140   18141)	25.4"   35.4"
Width (18140   18141)	20.5"   20.5"
Height (18140   18141)	15.9"   15.9"
Warranty	Limited Lifetime

### Chrome Oxygen Cylinder Rack



Item #	For Use With	UOM
18111	6 D or E Cylinders	1/cs
18112	12 D or E Cylinders	1/cs
18113	12 M6 Cylinders	1/cs

- Chrome plated finish, alloy carbon steel.
- Mounting brackets on bottom for in-truck installation.
- Heavy-duty welded construction.

**specifications**

Weight (18111   18112   18113)	6.6 lbs   11.3 lbs.   8.9 lbs.
Length (18111   18112   18113)	15.6"   20.3"   16.7"
Width (18111   18112   18113)	10.2"   15.6"   12.0"
Height (18111   18112   18113)	9.3"   9.3"   9.3"
Warranty	Limited Lifetime

### Chrome Oxygen Economy Cylinder Rack



Item #	For Use With	UOM
18114	6 C, D, or E Cylinders	1/cs
18116	6 M6 Cylinders	1/cs

- Keeps cylinders upright and securely stored.
- Chrome plated finish, alloy carbon steel.

**specifications**

Weight (18114   18116)	3.0 lbs   2.2 lbs.
Length (18114   18116)	15.0"   11.6"
Width (18114   18116)	10.2"   7.9"
Height (18114   18116)	8.5"   5.3"
Warranty	Limited Lifetime