

TECHNICAL DATA

SP196 Rev E/03-16

Miller Titan™ Non-Stretch Harness

Description

Titan™ Non-Stretch Harnesses are constructed of lightweight polyester webbing.

Materials

Webbing:	1-3/4 in. Polyester
Elastic Keepers:	Elastic
Thread:	Polyester
D-Ring*	Clear Chromate Finished Carbon Steel
Buckles*	Clear Chromate Finished Carbon Steel
Grommets*	Stainless steel
Label Pack:	Evoprene, Nylon
Label Materials:	Valeron

* All hardware meets ASTM (50) fifty-hour salt spray test requirements

Technical

Max Working Load:	400 lbs. (181.4 kg)
Minimum Tensile	
- D-Ring	5,000 lbs. (22 kN)
- Buckles	4,000 lbs. (18 kN)
- Thread:	42 lbs. (0.19 kN)
- Webbing:	5,000 lbs. (22 kN)

Certification

Meets applicable OSHA 1926.502, ANSI A10.32, Z359.11-14 and CSA Z259.10 standards.



Model Number	D-Rings	Shoulder Strap	Leg Strap	Chest Strap	Special Features	Weight
T2000/UAK	Back	N/A	Mating	Mating	Sub-Pelvic Strap & Lanyard Ring	2.25 lbs. (1.02 kg)
T2007/UAK	Back & Side	N/A	Mating	Mating	Sub-Pelvic Strap & Lanyard Ring	2.93 lbs. (1.33 kg)
T4000/UAK	Back	Friction	Mating	Mating	Sub-Pelvic Strap & Lanyard Ring	2.25 lbs. (1.02 kg)
T4500/UAK	Back	Friction	Tongue	Mating	Sub-Pelvic Strap & Lanyard Ring	2.18 lbs. (0.99 kg)
T4007/UAK	Back & Side	Friction	Mating	Mating	Sub-Pelvic Strap & Lanyard Ring	2.85 lbs. (1.29 kg)
T4507/UAK	Back & Side	Friction	Tongue	Mating	Sub-Pelvic Strap & Lanyard Ring	3.20 lbs. (1.45 kg)
T4577/UAK	Back & Side	Friction	Tongue	Mating	Sub-Pelvic Strap, Lanyard Ring, Tool Belt, Back Pad & Side D-Rings	4.87 lbs. (2.21 kg)

Model numbers listed are for universal size (L/XL). Harnesses are also available in small/medium and XXlarge by replacing the “U” in the model number with “S/M” or “XXL” (Ex.T4500/S/MAK).

Limitless Possibilities. Ask the Expert.

Technical Service: 800.873.5242
www.millerfallprotection.com

Honeywell Industrial Safety

900 Douglas Pike
Smithfield, RI 02917

USA

Phone: 800.430.5490
Fax: 800.322.1330

Canada

Phone: 888.212.7233
Fax: 888.667.8477

⚠ This equipment should only be used after reading and understanding the manufacturer's instructions. Failure to follow instructions could result in serious injury or fatality.